




Part Number : [461130203](#)
Product Description : 1.27mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 20 Signal Contact, Select Gold (Au) Plating, with BMI Guides
Series Number : 46113
Status : Active
Product Category : Board-to-Board Connectors
Engineering Number : 46113-0163



Documents & Resources

Drawings

[461130203_sd.pdf](#)
[PK-46114-003-001.pdf](#)

3D Models and Design Files

[461130203_stp.zip](#)
[SYM-46113-0203-001.zip](#)

Specifications

[AS-46114-001-001.pdf](#)
[PS-46114-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS

- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	46113
Description	1.27mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 20 Signal Contact, Select Gold (Au) Plating, with BMI Guides
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Product Name	EXTreme LPHPower
UPC	800756886091

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Grounding to PCB	No
Voltage - Maximum	250V AC (RMS)/DC

Physical

Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black

Durability (mating cycles max)	250
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.960/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tube
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	20s - 0p
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

EXTreme LPHPower Right-Angle Plugs	<u>45985</u>
---------------------------------------	--------------

This document was generated on Mar 02, 2025