



SIMATIC ET 200SP, Digital input module, DI 8x 24V DC Standard, type 3 (IEC 61131), sink input, (PNP, P-reading), Packing unit: 1 piece, fits to BU-type A0, Colour Code CC01, input delay time 0,05..20ms, module diagnostics for: short-circuit of sensor supply, wire break, supply voltage

General information	
Product type designation	DI 8x24 VDC ST
HW functional status	From FS02
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC01
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• suitable for operation on PROFINET R1 IMs	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	V5.5 SP3 or higher
• PCS 7 configurable/integrated from version	V8.1 SP1
• PCS neo can be configured/integrated from version	V3.1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DI	Yes
• Counter	No
• Oversampling	No
• MSI	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	50 mA; All channels are supplied from the encoder supply
Encoder supply	
Number of outputs	8
Output voltage, min.	19.2 V
Short-circuit protection	Yes; per module
24 V encoder supply	
• 24 V	Yes

<ul style="list-style-type: none"> • Short-circuit protection • Output current, max. • Output current per channel, max. • Output current per module, max. 	Yes 700 mA 700 mA 700 mA
Power loss	
Power loss, typ.	1 W; 24 V, 8 inputs supplied via encoder supply
Address area	
Address space per module	
<ul style="list-style-type: none"> • Inputs 	1 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	Yes
<ul style="list-style-type: none"> • Mechanical coding element • Type of mechanical coding element 	Yes Type A
Selection of BaseUnit for connection variants	
<ul style="list-style-type: none"> • 1-wire connection • 2-wire connection • 3-wire connection • 4-wire connection 	BU type A0 BU type A0 BU type A0 with AUX terminals or potential distributor module BU type A0 + Potential distributor module
Digital inputs	
Number of digital inputs	8
Digital inputs, parameterizable	Yes
Sourcing/sinking input	P-reading
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Input voltage	
<ul style="list-style-type: none"> • Rated value (DC) • for signal "0" • for signal "1" 	24 V -30 to +5 V +11 to +30V
Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
<ul style="list-style-type: none"> — parameterizable — at "0" to "1", min. — at "0" to "1", max. — at "1" to "0", min. — at "1" to "0", max. 	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms (in each case + delay of 30 to 500 µs, depending on line length) 0.05 ms 20 ms 0.05 ms 20 ms
Cable length	
<ul style="list-style-type: none"> • shielded, max. • unshielded, max. 	1 000 m 600 m
Encoder	
Connectable encoders	
<ul style="list-style-type: none"> • 2-wire sensor — permissible quiescent current (2-wire sensor), max. 	Yes 1.5 mA
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
<ul style="list-style-type: none"> • Diagnostic alarm 	Yes
Diagnoses	
<ul style="list-style-type: none"> • Diagnostic information readable • Monitoring the supply voltage — parameterizable • Monitoring of encoder power supply • Wire-break • Short-circuit 	Yes Yes Yes Yes; Module-by-module, optional protective circuit for preventing wire-break diagnostics in the case of simple encoder contacts: 25 kOhm to 45 kOhm Yes; Module-wise Yes; Module-wise
Diagnostics indication LED	
<ul style="list-style-type: none"> • Monitoring of the supply voltage (PWR-LED) • Channel status display 	Yes; green PWR LED Yes; green LED

• for channel diagnostics	No	
• for module diagnostics	Yes; green/red DIAG LED	
Potential separation		
Potential separation channels		
• between the channels	No	
• between the channels and backplane bus	Yes	
• between the channels and the power supply of the electronics	No	
Isolation		
Isolation tested with	707 V DC (type test)	
Standards, approvals, certificates		
Suitable for safety functions	No	
Ecological footprint		
• environmental product declaration	Yes	
Global warming potential		
— global warming potential, (total) [CO2 eq]	15.9 kg	
— global warming potential, (during production) [CO2 eq]	3.69 kg	
— global warming potential, (during operation) [CO2 eq]	12.7 kg	
— global warming potential, (after end of life cycle) [CO2 eq]	-0.495 kg	
Ambient conditions		
Ambient temperature during operation		
• horizontal installation, min.	-30 °C; < 0 °C as of FS02	
• horizontal installation, max.	60 °C	
• vertical installation, min.	-30 °C; < 0 °C as of FS02	
• vertical installation, max.	50 °C	
Altitude during operation relating to sea level		
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual	
Absolute humidity		
• dew point, min.	-60 °C; suitable for dry room applications	
Dimensions		
Width	15 mm	
Height	73 mm	
Depth	58 mm	
Weights		
Weight, approx.	28 g	
Classifications		
	Version	Classification
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05
Approvals / Certificates		
General Product Approval		



[China RoHS](#)

[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[CCC-Ex](#)

[EM](#)

For use in hazardous locations

Maritime application



[Type Examination Certificate](#)



[Miscellaneous](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

Environment

[KR \(Korean Register of Shipping\)](#)



last modified:

2/1/2026