

1825261-1 Product Details



1825261-1

TE Internal Number: 1825261-1

Active

Slide Switches

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 2 Positions
- Double Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Top
- Actuator Color = Black
- MSS Series

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, MSS 2200 SERIES, VERTICAL](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Double Throw
- Actuator Style = Top
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Instrumentation
- Termination Type = PC
- PCB Mount Retention = With

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

Body Related Features:

- [Number of Positions](#) = 2
- Actuator Color = Black
- Series = MSS
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 5.33 [0.210]
- PCB Mount Retention Type = Guide Posts
- Actuator Length (mm [in]) = 2.30 [0.090]
- Actuator Material = Polyester
- Actuator Travel = 2.00 [.079]

Contact Related Features:

- Contact Plating = Silver

Housing Related Features:

- UL Flammability Rating = UL 94V-0

Configuration Related Features:

- Threaded Case = Without
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch

BOOKMARK

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map


Customer Support

Email or Chat with Us
Find a Phone Number
Search Knowledge Base
Manage Your Account

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

