




NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.




MATING FACE
ASSY: W7A81-8SG-3ES SHOWN





RECOMMENDED PANEL CUTOUT



ASSEMBLED VIEW
ASSY: W7A81-8SG-3ES SHOWN




ASSEMBLED VIEW
ASSY: W7A82-8SG-300 SHOWN



WIRING END
ASSY: W7A82-8SG-300 SHOWN

RoHS COMPLIANT

CONNECTOR P/N	POSITIONS		CONTACT STYLE	EPOXY
	#16	#26		
W7A80-8SG-300	2	6	CRIMP	(NONE)
W7A81-8SG-300			PC TAIL	(NONE)
W7A81-8SG-3ES			PC TAIL	ES
W7A82-8SG-300			SOLDER	(NONE)
W7A82-8SG-3ES			SOLDER	ES



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

PRELIMINARY

0A		PNK		01/15/15		PDR 14001 PRELIMINARY											
REV.		INIT.		DATE		DESCRIPTION											
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.						ORIG. DRAWN BY: PNK			DATE: 01/15/15			conxall 601 E. WILDWOOD VILLA PARK, IL 60181					
						CHECKED BY:											
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED: TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16						APPROVED BY:						TITLE: PANEL-MOUNT CONNECTOR 2-16 + 6-26 SOCKET CONTACTS MINI-CON-X POWER/SIGNAL CUSTOMER: STANDARD PRODUCT					
						SCALE NTS		SIZE B		SHEET 1 OF 1							
▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX						FILE: W7A8X-8SG-3XX_CD			DIRECTORY: SLW			PART NUMBER: W7A8X-8SG-3XX			REV 0A		