



## 1520213-4 Product Details

[!\[\]\(cf531ed27e91483460120fcc057b3901\_img.jpg\) Share](#) [!\[\]\(34fde9b7c74442c0438f550a41236260\_img.jpg\) Print](#) [!\[\]\(f3ffd03e145adb5d0f6f54d9f4fb82fd\_img.jpg\) Email](#)

1520213-4

TE Internal Number: 1520213-4



### Power Toggle Switches

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 17.48 mm
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[!\[\]\(23a2e9ddc7bb0ef55393d38b772a848d\_img.jpg\) Add to My Part List](#) [!\[\]\(cdc5d03852d90f3a0d1df88fd5fca224\_img.jpg\) Request Sample](#) [!\[\]\(2d0e2388c5813d8a3a70734d8b66a310\_img.jpg\) Find Similar Products](#) [!\[\]\(bdaaf4c97b2c34e53b2e8ba5bd765616\_img.jpg\) Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Related Products:

- [Tooling](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw
- Termination Type = Screw-In Terminal

#### Configuration Features:

- Bushing Length (mm [in]) = 11.91 [0.469]

#### Electrical Characteristics:

- UL/CSA 125V Current Rating (A) = 16
- UL/CSA 250V Current Rating (A) = 8
- UL/CSA 125V Horse Power Rating (hp) = 1.00

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Housing Features:

- Toggle Length (mm [in]) = 17.48 [0.688]
- Toggle Style = Baton

#### Other:

- Brand = Alcoswitch

### Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

### Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

### Customer Support

[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events &amp; Technology Updates

Enter your email address 