



HONEYWELL PART NUMBER
1SM3
PRODUCT CODE: TWA0300
JG-80011J

REV	DOCUMENT	CHANGED BY	CHECK
13	0034444	JA 15OCT07	PSR



- NOTES
- 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX. DIA. ON .375^{±.002} CENTERS
 - 2- TERMINALS ARE PLATED FOR SOLDERING
 - 3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.:
-
REPLACES
-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± 0.040 ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± 0.0005 ANGLES ± 2		DRAWN	JA	15OCT07	Honeywell			
OPERATING FORCE-----3-5 OZ.		CONTACT ARRANGEMENT SPDT					CHECK	PSR	15OCT07				
RELEASE FORCE-----1 OZ. MIN.		30 VOLTS DC RATING			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE SWITCH-BASIC						
			SEA LEVEL	50,000 FT									
DIFFERENTIAL TRAVEL-----.004 MAX.		INDUCTIVE	3 AMP	2.5 AMP									
		RESISTIVE	5 AMP	5 AMP									
OVERTRAVEL-----.005 MIN.		MAXIMUM INRUSH 24 AMP			INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		SIZE	TYPE	DRAWING NAME		REV		
		APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4				B	I	1SM3		13	
			UL, CSA	5A, 250 VAC				BRAND L4	SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1				
					THIRD ANGLE PROJECTION 		RASTER						