



© 2016 AFCl

Amphenol
FCI

D

2 3

2

3

4

4

5

5




6

6


Part Number	CONFIGURATION													
	POS	12	11	10	9	8	7	6	5	4	3	2	1	
10126492-X01LF	D	—	—	—	—	—	—	—	—	—				
	C	—	—	—	—	—	—	—	—	—				
	B	—	—	—	—	—	—	—	—	—				
	A	—	—	—	—	—	—	—	—	—				
Part Number	CONFIGURATION													
	POS	12	11	10	9	8	7	6	5	4	3	2	1	
10126492-X02LF	D	—	—	—	—	—	—	—	—	—	—	—	—	
	C	—	—	—	—	—	—	—	—	—	—	—	—	
	B	—	—	—	—	—	—	—	—	—	—	—	—	
	A	—	—	—	—	—	—	—	—	—	—	—	—	

SELECTIVE CONTACT LOADING

NOTE: " — " POSITION LOADED



REFER NOTE-2
10126492-XYLFF



LAYOUT FOR P.C.B

scale : 2.0



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE GS-12-447

FOR PTH DETAILS REFER DRAWING NO : 58351.

NOTES:

1. MATERIAL : BODY : LCP UL94-V0 : CONTACT : COPPER ALLOY.
2. FOR PLATING SPECIFICATION REFER DRAWING NO : 10159408
3. PRODUCT SPECIFICATION : GS-12-002
4. THESE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004.
8. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family METRAL			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	NEW RELEASE	QIND	2013-11-04	angles linear	.X±0.3		mm		METRAL FEM. 4 ROW SL STRAIGHT PRESS FIT				
B	ELX-DG-19619	MIC	2014-12-03		.XX±0.13				PCB THICKNESS: 2.4 mm MINIMUM				
C	ELX-I-38990	MINI	2020-11-17		0°±2° .XXX±0.050				scale —				
				dr	MICHAEL SONG	2014-12-03			dwg no		sheet 1 of 1	size	
				enr	ARUN	2020-11-17			10126492		A3		
				chr	ALEX BABU	2020-11-17							
				appd	SANOJ	2020-11-17							
sheet index		revision sheet	C 1							type Product Customer Drawing			