

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BA-1RV543510-A2

BA-1RV543510-A2

PAGE 1 OF 1

REPLACES X 71635-BA

RELEASE NO. PR-11436T

DRAWING
NUMBER

4

ISSUE

CHECK

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	CO-77590	SAD	8 JUN 94
C	CO93346	DLT	31 AUG 98

CHECK

10 AUG 82

C E B


82 CHECK

AUG

D J S

FORMTEK


FO-52848-A



MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 5 OZ MAX
RELEASE FORCE ----- 1 1/2 OZ MIN
PRETRAVEL ----- .109 MAX
DIFFERENTIAL TRAVEL ----- .011 MAX
OVERTRAVEL ----- .020 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L65

L288
L299
L306

15A-125, 250 OR 480 VAC
1/2HP-125 VAC; 1HP-250 VAC

CE D UL 16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	17/64	X	0.07/00
ONE PLACE	X,X	0.4/016	X,X	0.39/016
TWO PLACES	X,XX	0.16/006	X,XX	0.15/006
THREE PLACES	X,XXX		X,XXX	
ANGLES				

DESIGN UNITS ☐ IN METRIC ☒ US CUSTOMARY

WEIGHT .063 LB