



Part Number : [2058563020](#)

Product Description : QSFP-DD-to-8 SFP56 (zSFP+)
Passive Cable Assembly, 56 Gbps, 28 AWG, 2.0m
Length

Series Number : 205856

Status : Active

Product Category : High-Speed I/O Cable
Assemblies



Documents and Resources

Drawings


[2058563020 sd.pdf](#)

Specifications

[2058561005-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	205856
Description	QSFP-DD-to-8 SFP56 (zSFP+) Passive Cable Assembly, 56 Gbps, 28 AWG, 2.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP-DD-to-8 SFP56, QSFP-DD-to-8 zSFP+
Product Name	QSFP-DD,zSFP Plus,zSFP+
Type	Pluggable
UPC	191128873512

Electrical

Data Rate	56.0 Gbps
Impedance	100Ω

Physical

Cable Bundling	Woven Braid
Cable Length	2.0m
Circuits (Loaded)	MSA
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Zinc Die Cast
Material - Plating Mating	Gold
Net Weight	827.000/g
Packaging Type	Bag

Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Temp-Flex Twinax
Wire Size (AWG)	28

This document was generated on Dec 18, 2025