


A. QUANTITY: SINGLE PACK
B. BAG TO BE MARKED: AMPHENOL RF, 135111-01-XX.XX, AND DATE CODE



TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

☒ FREQUENCY : DC TO 3.0 GHz	☒ CONTINUITY
☐ VSWR : ____1 MAX	☒ HI-POT : 500 VRMS
☐ INS. LOSS : ____ dB MAX	☐ OTHER

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE: <0.5mm = ±0.05mm [<0.020 = ±0.002] 0.5 - 6mm = ±0.1mm [>0.020 - 0.236 = ±0.004] >6.00 - 30mm = ±0.2mm [>0.236 - 1.181 = ±0.008] >30.00 - 120mm = ±0.3mm [>1.181 - 4.725 = ±0.012]			MATERIAL --			TITLE SMA RIGHT ANGLE CRIMP PLUG TO SMA BULKHEAD CRIMP JACK, USING RG-316/U COAXIAL CABLE, VARIOUS LENGTHS.			Amphenol RF																	
												THIRD ANGLE PROJ. 			REFERENCE			EAR#			SIZE			DRAWING NO. 135111-01-XX-XX			REV		
												B			ENGR.1 KARTHIK R			ENGR.2 LONPON			DATE 11-May-22			SHEET NO. 2 OF 2			SCALE: 3.0:1.0		
ANGLES = ±1°															ITEM NO. 135111-01-XX-XX			PART NO. 135111-01-XX-XX											