

FL PLUG RJ45 GN/2 - RJ45 connector



2744571

<https://www.phoenixcontact.com/us/products/2744571>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, connection cross section: AWG 26- 24, cable outlet: straight, color: green, Ethernet

Your advantages

- Set of 2 connectors
- Easy installation with a crimping tool
- With gray bend protection sleeve: recommended for straight, uncrossed cables

Commercial data

Item number	2744571
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAG
Catalog page	Page 50 (C-5-2017)
GTIN	4017918607586
Weight per piece (including packing)	19 g
Weight per piece (excluding packing)	18.8 g
Customs tariff number	85366990
Country of origin	US

FL PLUG RJ45 GN/2 - RJ45 connector



2744571

<https://www.phoenixcontact.com/us/products/2744571>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
Type	RJ45
Cable outlet	straight
Positions/contacts	8P8C

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Contact resistance	< 100 mΩ (max.)
Frequency range	100 MHz
Insulation resistance	> 500 MΩ
Nominal current I_N	1.5 A
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps

Connection data

Connection technology

Connection method	Crimp connection
Connection cross section AWG	26 ... 24 (solid) 26 ... 24 (flexible)
Conductor cross section	0.14 mm ² ... 0.22 mm ² (solid) 0.14 mm ² ... 0.22 mm ² (flexible)

Dimensions

Width	13.7 mm
Height	13.1 mm
Length	13.7 mm

Material specifications

Color	green
Flammability rating according to UL 94	V0
Housing material	Plastic

FL PLUG RJ45 GN/2 - RJ45 connector



2744571

<https://www.phoenixcontact.com/us/products/2744571>

Contact material	Phosphor bronze
Contact surface material	Au/Ni
Contact carrier material	PC
Locking latch material	PC

Cable/line

External cable diameter	4.6 mm ... 5.8 mm
Cable cross section	0.14 mm ²
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	min. 2500
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Mounting

Mounting type	Crimp connection
---------------	------------------

FL PLUG RJ45 GN/2 - RJ45 connector



2744571

<https://www.phoenixcontact.com/us/products/2744571>

Classifications

ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FL PLUG RJ45 GN/2 - RJ45 connector



2744571
<https://www.phoenixcontact.com/us/products/2744571>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com