






LOC		DIST		REVISIONS			
P	D	REV	PER	DESCRIPTION	DATE	DWN	APVD
GP	00						





- 1 PART NUMBER, AND DATE CODE MARKED IN AREA SHOWN.
- 2 MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, UL94 V-0
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING:
SIGNAL CONTACTS - .000050 MIN Ni UNDER ALL.
.000030 MIN Au ON CONTACT AREA.
.000100 MIN Sn AT PCB INTERFACE.
POWER CONTACTS - .000050 MIN Ni UNDER ALL.
.000030 MIN Au ON CONTACT AREA.
.000100 MIN Sn AT PCB INTERFACE.
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7 PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 HOLE.
- 8 VARIABLE DIMENSION, SEE VIEW ON SHEET 4



.200	3.375	3.325	1.050	.375	3.675	24S + 12HDP	I-6600120-0
.250	2.450	2.400	1.050	.375	2.750	24S + 6P	6600120-9
.250	3.450	3.400	1.050	.375	3.750	24S + 10P	6600120-8
.250	3.450	3.400	1.050	.375	3.750	24S + 10P	6600120-3
.250	2.450	2.400	1.050	.375	2.750	24S + 6P	6600120-2
8	3.850	3.800	.900	.400	4.150	12S + 11P	6600120-1
DIM T	DIM D	DIM U	DIM W	DIM K	DIM L	DESCRIPTION	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. GRZYBOWSKI 13JUN05	TE Connectivity	
DIMENSIONS: INCHES		CHK M. PERCHERKE 13JUN05	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. PERCHERKE	RIGHT ANGLE HEADER ASSEMBLY W/GUIDES DUAL BEAM XL	
9 PLC ±.01		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
3 PLC ±.005		108-1973	RESTRICTED TO	
5 PLC ±.0020		APPLICATION SPEC	A100779C=6600120	
4 PLC ±.0020		114-13038	SCALE 4:1 SHEET 1 OF 4 REV D	
ANGLES ±2°		WEIGHT	CUSTOMER DRAWING	
FINISH				

PART NUMBER	ROWS		SIGNAL						POWER												
			1	2	3	4	5	6	PI	P2	P3	P4	P5	P6	P7	P8	P9	PI0	PI1	PI2	
1-6600120-0	D C B A	 HD	J	J	J	J	J	E	 PS	 PS	 PS	 PS	 PS	 PS	 PS	 PS	 PS	 PS	 PS	 PS	 PS
			K	K	K	F	K	K													
			N	N	N	G	N	N													
			S	H	S	H	S	S													
24S + 12HDP																					

