



HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45
35410 Hungen
Germany

phone: +49 (0) 6402/808-0

fax: +49 (0) 6402/808-60

email: info@hahn-trafo.de

Data sheet: BV EI 306 2071

Size 6 a: height 33.8 mm

3,2 VA

ta 40/F

BV EI 306 ...

Several hundreds of typen provide high electrical safety and long service-life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open-circuit (no-load) loss capacity are also available in the range.

absolutely short-circuit-proof

minimal size

test certifications to ENEC 10-, VDE, UL- and CSA-regulations

vaccum encapsulated, bobbin with dual chamber windings

temperature class ta 40°C/F and ta 70°C/F

hight electrical safety and long service-life properties


individually tested with certificate

excellent temperature fluctuation resistance properties


self-extinguishing cast housing and sealing material




| Article no. BV | Output ta 40°C/F | prim.V | Connecting pins | Operating point sec. ± 5% | Connecting pins | No-load voltage V ± 5% |
|----------------|------------------|--------|-----------------|------------------------------|-----------------|---------------------------|
| BV EI 306 2071 | 3,2 | 230 | 1-5 | 9 V 356 mA | 7-9 | 16,3 |



Ansicht auf die Stifte



Lötstift 0,6x0,8/
Rundpin ø0,8



Maße ohne Toleranzangabe ± 0,3 mm,
Ausführungsänderungen vorbehalten