



A Product Line of  
Diodes Incorporated



## PRODUCT SPECIFICATION

|                   |                                                      |
|-------------------|------------------------------------------------------|
| NOMINAL FREQUENCY | 50.000000 MHz                                        |
| PRODUCT TYPE      | TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR |
| SPEC. NO. ( P/N ) | HX3150003Q                                           |
| ISSUE DATE        | August 9, 2022                                       |
| VERSION           | C                                                    |

### Diodes Incorporated

No.2, Ziqiang 5th Rd., Zhongli Industrial Park,  
Zhongli Dist., Taoyuan City 32063, Taiwan (R.O.C.)  
TEL: 886-3-451-8888  
FAX: 886-3-461-3865  
<https://www.diodes.com>

\*Pb-free  
\*RoHS Compliant  
\*HF-Halogen Free  
\*REACH Compliant  
\*AEC-Q200 Compliant  
\*MSL: Level 1

## TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

***HX3150003Q***

VER. C 9-Aug-22

## VERSION HISTORY

[illegible]

# TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX3150003Q**

VER. C 9-Aug-22

## ELECTRICAL SPECIFICATIONS

**SRe Part Number : HX3150003Q**

| Item                            | Symbol                         | Specifications      | Units | Notes                                |
|---------------------------------|--------------------------------|---------------------|-------|--------------------------------------|
| Nominal Frequency               | Fo                             | 50.000000           | MHz   |                                      |
| Frequency Stability             | FT                             | ± 50                | ppm   | **See note                           |
| Operating Temperature Range     | TR                             | -40 to +125         | °C    |                                      |
| Supply Voltage                  | V <sub>DD</sub>                | +2.25 to +3.6       | V     | at +3.3V Typ.                        |
| Logic Type                      | LT                             | LVC MOS             |       |                                      |
| Supply Current, Output Enabled  | I <sub>DD</sub> /OE            | 20                  | mA    | Max.                                 |
| Supply Current, Output Disabled | I <sub>DD</sub> /OD            | 100                 | μA    | Max.                                 |
| Duty Cycle (Symmetry)           | DC/SY                          | 45 / 55             | %     | Measured 50% of Waveform             |
| Rise / Fall Time                | T <sub>R</sub> /T <sub>F</sub> | 2.5                 | ns    | Max. measured 20/80% of Waveform     |
| Output Voltage "0" Level        | V <sub>OL</sub>                | 10% V <sub>DD</sub> | V     | Max at I <sub>OL</sub> = 4.0mA Min.  |
| Output Voltage "1" Level        | V <sub>OH</sub>                | 90% V <sub>DD</sub> | V     | Min at I <sub>OH</sub> = -4.0mA Max. |
| Output Load                     | CL                             | 15                  | pF    | Max.                                 |
| Jitter, Phase                   | RMS                            | 1                   | ps    | Max. 12KHz ~ 20MHz Frequency Band    |
| Jitter, Accumulated             | RMS(1-σ)                       | 4                   | ps    | Max. 20,000 Consecutive Periods      |
| Jitter, Peak to Peak            | Pk-Pk                          | 40                  | ps    | Max. 100,000 Random Periods          |
| Start Up Time                   |                                | 2                   | ms    | Max.                                 |
| Storage Temperature Range       |                                | -55 to +125         | °C    |                                      |

**\*\*Stability includes all combinations of Operating Temperature, Load changes, rated Input (Supply) Voltage changes, Initial Calibration Tolerance (25°C), Aging (1 year at 25°C Average Effective Ambient Temperature), Shock and Vibration.**

### Output Enable / Disable Function

| Parameter                                                | Min.               | Typ. | Max.               | Units | Notes          |
|----------------------------------------------------------|--------------------|------|--------------------|-------|----------------|
| Input Voltage (Pin1), Output Enable                      | 0.7V <sub>DD</sub> |      |                    | V     | Or Open        |
| Input Voltage (Pin1), Output Disable (low power standby) |                    |      | 0.3V <sub>DD</sub> | V     | Output is Hi-Z |
| Internal Pullup Resistance                               | 30                 |      |                    | KΩ    |                |
| Output Disable Delay                                     |                    |      | 50                 | ns    |                |




# TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**HX3150003Q**

VER. C 9-Aug-22

## TEST CIRCUIT



## OUTPUT WAVEFORM



# TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX3150003Q**

VER. C 9-Aug-22

## AEC-Q200 RELIABILITY TEST SPECIFICATIONS:

### 1. Initial

- 1.1 Physical Dimensions: JESD22, Method JB1-100
- 1.2 External Visual: MIL-STD-883, Method 2009
- 1.3 Freq. Vs. Temperature: Per Specification/Datasheet

### 2. Mechanical


- 2.1 Mechanical Shock: MIL-STD-202 Method 213
- 2.2 Vibration: MIL-STD-202 Method 204
- 2.3 Solderability: J-STD-002
- 2.4 Board Flex: AEC Q200-005
- 2.5 Terminal Strength (SMD): AEC Q200-006

### 3. Environmental

- 3.1 Temperature Cycle: JESD22, Method JA-104
- 3.2 Resistance to Solder Heat: MIL-STD-202 Method 210
- 3.3 High Temperature Operating Life: MIL-STD-202, Method 108
- 3.4 High Temperature Exposure: MIL-STD-202, Method 108
- 3.5 High Temperature & High Humidity: MIL-STD-202, Method 103
- 3.6 Thermal Shock: MIL-STD-202, Method 107
- 3.7 ESD Testing : JEDEC JS-001 / JEDEC JS-002
- 3.8 Latch up Testing : JESD78

## SUGGESTED IR REFLOW PROFILE

\*As per IPC-JEDEC J-STD-020D



Note:


|   | Stage        | Temperature | Time       |
|---|--------------|-------------|------------|
| A | Preheat      | 150~200°C   | 60~120 Sec |
| B | Primary Heat | 217°C       | 60~150 Sec |
| C | Peak         | 260°C       | 10 Sec     |

# TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**HX3150003Q**

VER. C 9-Aug-22


## MARKING




## MECHANICAL DRAWINGS ( Scale: None. Dimensions are in mm.)



### Recommended Land Pattern\*



\*External high-frequency power decoupling is recommended.(see test circuit for minimum recommendation). To ensure optimal performance, do not route traces beneath the package.



(Bottom View)


| Pin | Function        |
|-----|-----------------|
| 1   | OE              |
| 2   | Ground          |
| 3   | Clock Output    |
| 4   | V <sub>DD</sub> |

# TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

**HX3150003Q**

VER. C 9-Aug-22

## TAPE&REEL




1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.

# TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


**HX3150003Q**

VER. C 9-Aug-22


## PACKING



3000pcs-Product Tape



Blue Qualified Label



Storeroom Label

