







CIRCUIT DIAGRAM
BOTTOM VIEW




Specifications:

Contact rating:	350 mA, 30 V DC
Contact resistance:	20 mOhm max.
Insulation resistance:	100 MOhm min. at 500 V DC
Dielectric strength:	500 V AC, 50 Hz for 1 minute
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Mechanical life:	10 000 cycles
Operating force:	250 +/-100 gf
Soldering conditions:	auto-soldering, pre-heat: max. 100°C, max. 100 sec.;
	wave soldering: max. 260°C, 5 sec.

Material:

Terminal: brass, silver plated
Base: phenolic resin
Frame: steel, nickel plated
Contact: brass, silver plated
Spring: SWC, tempered
Slider: PA66, UL94-HB, black

HOLE LAYOUT ± 0.05



Compliance: RohS III (2015/863/EU)

Tolerances: up to 10: ± 0.2 mm above 10-50: ± 0.3 mm			Date	Name	MFP 140	
			01/10	dr		
					30 19 88	
Specifications	01/21	dr	knitter-switch			Page
Modifications	Date	Name				1/1