




**Part Number :** [1731130058](#)  
**Product Description :** FCT High-Density D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, 15 Circuits  
**Series Number :** 173113  
**Status :** Active  
**Product Category :** D-Sub Connectors  
**Engineering Number :** CT09-15P




Documents & Resources

**Drawings**  
[1731130058\\_sd.pdf](#)

**Specifications**  
[1731120006-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen
- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
  - IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	D-Sub Connectors
Series	173113
Description	FCT High-Density D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, 15 Circuits
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	High Density
UPC	889056324410

#### Electrical

Current - Maximum per Contact	3.0A
Shielded	Yes

#### Physical

Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Black
Gender	Male
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Steel
Net Weight	5.000/g
Number of Rows	3
Orientation	Straight
Packaging Type	Tray
Panel Mount	Rear

Panel Mount Method	Flange
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	1.98mm
Pitch - Termination Interface	1.98mm
Plating - Contact	Gold over Nickel
Plating - Shell	Nickel
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-55° to +105°C
Termination Style	Solder Cup
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Wire Size (AWG)	22

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	FCT High-Density D-Sub, Size 1, 15 Position, Socket

---

This document was generated on Apr 26, 2025