




REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE

8P and 8P following no reinforcement.



02P

NOTES1:

UL Standard

1. Rated voltage/current : 150V / 4A

2. Withstanding voltage : AC1300V/1Min.

IEC Standard

1.

Pollution degree	2
Overvoltage category	II
Rate Impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	5A

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009




2. Pitch : 2.5mm, Poles : N=02~12P

3. Operating temperature: -40°C~+105°C

4. Undimensioned tolerances:


Pitch range	in mm	Nominal dimension	range	mm
Over	6	TO	Over	0.1/10
TO	10	TO	TO	150
TO	24	TO	TO	<
6	10	30	60	100
		60	100	150
		±0.15	±0.20	±0.30
		±0.30	±0.50	±0.70
		±1.00	±1.30	±2

5. RoHS Compliance



15EDGRC - 2.5 - XXP - 1Y - 00A (H)  
 (Series No.) (Pitch) (Poles) (Color) : 1. (Grey)  
 2. (Blue)  
 3. (Black)  
 4. (Green)  
 5. (Orange)  
 6. (Red)  
 7. (Transparent)  
 8. (Yellow)  
 9. (White)

2.5x(N-1)



DETACHED LISTS	
PART NO.:	/
APPD:	/
CHKD:	/
DRFT:	/
THIRD ANGLE PROJECTION	
NAME:	<b>DEGSON</b> NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
TITLE:	CUSTOMER DRAWING
DRAWING NO.:	/
REV	DO
SHEET	1/1
SCALE	1:1

