


## 746610-4 Product Details

[Live Product Chat](#)



### 746610-4

TE Part Number: 746610-4

✔ [Active](#)

[Add to Part List](#)

### Ribbon Cable Connectors (AMP-LATCH)

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

#### Product Highlights:

- Connector Type = DIP (Dual In Line Package)
- Number of Positions = 20
- Plug
- Without Mating Polarization
- Terminate To Printed Circuit Board

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [KIT, AMP-LATCH DIP PLUG, PREASSEMBLED, .100 X .100 C...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Connector, Round Conductor Cable, Paddleboard & Plug...](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [Connector-Specific Kit f/AMP-LATCH DIP Connectors](#) (PDF, English)

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version G)
- [3D Model](#) (IGES, Version G)
- [3D Model](#) (STEP, Version G)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Connector Type](#) = DIP (Dual In Line Package)
- [Number of Positions](#) = 20
- Gender = Plug
- [Mating Polarization](#) = Without
- [Mounting Ears](#) = Without
- PCB Retention Feature = No
- Mating Connector Lock = Without
- Strain Relief = Without
- With Cover Preassembled = Yes

#### Termination Related Features:

- [Solder Tail Contact Plating](#) = Bright Tin-Lead over Nickel

#### Body Related Features:

- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

#### Contact Related Features:

- [Contact Mating Area Plating Material](#) = Bright Tin-Lead over Nickel
- Contact Material = Phosphor Bronze

#### Housing Related Features:

- [Housing Color](#) = Black
- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0

#### Configuration Related Features:

- Cable Stop = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

#### Conditions for Usage:

- [Terminate To](#) = Printed Circuit Board

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)