



**Part Number :** [1200652313](#)

**Product Description :** Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, A-Coded, Female (90°) to Pigtail, 24 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length

**Series Number :** 120065

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 808001B41M100



---

## Documents and Resources

### Drawings

[1200652313\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## CE - Declaration of Conformity

## UKCA - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, A-Coded, Female (90°) to Pigtail, 24 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	889056029643

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

### Physical

Cable Diameter	6.40mm (.252")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded

Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	565.700/g
Orientation	90° to Pigtail
Poles	8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24

---

This document was generated on May 09, 2026