




AIM-121

Accessory Interface Module



**Antenna Required
(Not Included)**

For Easy Integration of Sensors

Order #	Description
AIM-121	Wireless Accessory Interface Module for Sensors

Dimensions	8.2" L x 2.3" W x 1.3" H (209mm L x 59mm W x 33mm H)
Input Power*	100 to 277 VAC +/- 10% (Max 305V) 47/64 Hz
Operating Environment	-40°C to +70°C
Radio	SNAP 2.4GHz ; 802.15.4 +20 dBm Transmit Power -103 dBm Receive Sensitivity
Sensor Inputs	0 - 10V (photocell sensors) 0 - 24V (all other sensors)
Sensor Power Supply	24VDC @ 50mA
Certifications	c(UL)us, FCC, IC, CE
Warranty	5 Years

See www.synapsewireless.com/warranty for warranty terms

* Single phase power supported

Note: 208V dual phase power is also supported, however the controller only switches one leg of this circuit. Please verify with an installer that this will not impact the design at the system level.

Specification Data	
Job Name	
Type	
Catalog #	
Comments	

Product Overview

The **AIM-121** is an accessory interface module that allows connection of two standard wired sensors to the SimplySNAP wireless lighting solution.

Features


- Self-healing SNAP Mesh Networking
- Seamlessly integrates into the SimplySNAP lighting control solution
- Direct Connect to 24V Occupancy Sensors and Photocells (consult sales for compatible list)
- Secure, over-the-air upgrades to support future enhancements
- Excellent RF Range — 1 mile LoS between controllers
- Available in a metal cased version with quick connect terminal blocks

Auxiliary Controls

To learn more, call or visit:
synapsewireless.com
(877) 982-7888



AIM-121 Wiring Diagram



Class 1 Terminal Block (accepts 12-28 AWG wires)	
Neutral	AC Return
Line*	100-277 VAC (+/- 10%)

*Single phase power supported
Note: 208V dual phase power is also supported, however the controller only switches one leg of this circuit. Please verify with an installer that this will not impact the design at the system level.

Class 2 Terminal Block (accepts 18-20 AWG wires)	
0-24V Input 1	Sensor Input 1
0-24V Input 2	Sensor Input 2
Common	Sensor DC Return
+24 VDC	Sensor Power Supply
Common	Sensor Power Supply Return

LED Indicators	Power LED: Power On
	Status LED: Reserved for future use

Fixture Antenna Kits

Part #	Description
KIT-ANT18-01	Outdoor Right Angle Antenna, 18" Cable with 14mm Bulkhead with O-ring
KIT-ANT18-02	Outdoor Straight Antenna, 18" Cable with 14mm Bulkhead with O-ring
KIT-ANT18-03	Outdoor Straight Stubby Antenna, 18" Cable with 14mm Bulkhead with O-ring
KIT-ANT18-04	Outdoor Right Angle Stubby Antenna, 18" Cable with 14mm Bulkhead with O-ring
KIT-ANT18-13-2.0	Indoor, Articulating Antenna, 2.4GHz, 2.0dBi Gain, 4"
KIT-ANT18-13-3.2	Indoor, Articulating Antenna, 2.4GHz, 3.2dBi Gain, 5"

Auxillary Controls