





1		2		3		4				
A	Performance Level									
	PL3 : 50 mating Cycles No Gas Test	PL2 : 250 mating Cycles 4 days Gas Test	S4 : 0,76µm Au or equivalent PdNi			Dimensions (mm)				
	Nb of Contacts	Part Number	Part Number	Part Number	Insulator Color	Contact Lenght ±0,3(mm)	A Max	B	E	
B	06	0918 506 7323	0918 506 6323	0918 506 5323	Grey	2,9mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7323	0918 510 6323	0918 510 5323			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7323	0918 514 6323	0918 514 5323			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7323	0918 516 6323	0918 516 5323			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7323	0918 520 6323	0918 520 5323			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7323	0918 526 6323	0918 526 5323			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7323	0918 530 6323	0918 530 5323			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7323	0918 534 6323	0918 534 5323			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7323	0918 540 6323	0918 540 5323			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7323	0918 550 6323	0918 550 5323			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7323	0918 560 6323	0918 560 5323			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7323	0918 564 6323	0918 564 5323			89,3	86,44	2,54 x 31 = 78,74	
C	06	0918 506 7323 001	0918 506 6323 001	0918 506 5323 001	Black	2,9mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7323 001	0918 510 6323 001	0918 510 5323 001			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7323 001	0918 514 6323 001	0918 514 5323 001			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7323 001	0918 516 6323 001	0918 516 5323 001			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7323 001	0918 520 6323 001	0918 520 5323 001			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7323 001	0918 526 6323 001	0918 526 5323 001			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7323 001	0918 530 6323 001	0918 530 5323 001			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7323 001	0918 534 6323 001	0918 534 5323 001			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7323 001	0918 540 6323 001	0918 540 5323 001			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7323 001	0918 550 6323 001	0918 550 5323 001			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7323 001	0918 560 6323 001	0918 560 5323 001			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7323 001	0918 564 6323 001	0918 564 5323 001			89,3	86,44	2,54 x 31 = 78,74	
D	06	0918 506 7321	0918 506 6321	0918 506 5321	Grey	4,5mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7321	0918 510 6321	0918 510 5321			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7321	0918 514 6321	0918 514 5321			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7321	0918 516 6321	0918 516 5321			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7321	0918 520 6321	0918 520 5321			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7321	0918 526 6321	0918 526 5321			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7321	0918 530 6321	0918 530 5321			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7321	0918 534 6321	0918 534 5321			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7321	0918 540 6321	0918 540 5321			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7321	0918 550 6321	0918 550 5321			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7321	0918 560 6321	0918 560 5321			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7321	0918 564 6321	0918 564 5321			89,3	86,44	2,54 x 31 = 78,74	
E	06	0918 506 7321 001	0918 506 6321 001	0918 506 5321 001	Black	4,5mm	15,4	12,78	2,54 x 2 = 5,08	
	10	0918 510 7321 001	0918 510 6321 001	0918 510 5321 001			20,5	17,86	2,54 x 4 = 10,16	
	14	0918 514 7321 001	0918 514 6321 001	0918 514 5321 001			25,6	22,94	2,54 x 6 = 15,24	
	16	0918 516 7321 001	0918 516 6321 001	0918 516 5321 001			28,1	25,48	2,54 x 7 = 17,78	
	20	0918 520 7321 001	0918 520 6321 001	0918 520 5321 001			33,2	30,56	2,54 x 9 = 22,86	
	26	0918 526 7321 001	0918 526 6321 001	0918 526 5321 001			40,8	38,18	2,54 x 12 = 30,48	
	30	0918 530 7321 001	0918 530 6321 001	0918 530 5321 001			45,9	43,26	2,54 x 14 = 35,56	
	34	0918 534 7321 001	0918 534 6321 001	0918 534 5321 001			51,0	48,34	2,54 x 16 = 40,64	
	40	0918 540 7321 001	0918 540 6321 001	0918 540 5321 001			58,6	55,96	2,54 x 19 = 48,26	
	50	0918 550 7321 001	0918 550 6321 001	0918 550 5321 001			71,5	68,66	2,54 x 24 = 60,96	
	60	0918 560 7321 001	0918 560 6321 001	0918 560 5321 001			84,2	81,36	2,54 x 29 = 73,66	
	64	0918 564 7321 001	0918 564 6321 001	0918 564 5321 001			89,3	86,44	2,54 x 31 = 78,74	
F	 All Dimensions in mm Original Size DIN A4		Scale 2:1	Free size tol.		Ref.				
	 All rights reserved Department EC PD - FR HARTING Electronics GmbH D-32339 Espelkamp		Created by DOUGE		Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2013-11-04	State Final Release		
			Title SEK 18 male right angled low profile					Doc-Key / ECM-Nr. 100552528/UGD/001/A 500000067002		
			Type TB	Number 09185XXX32X				Rev. A	Page 2/2	