



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL RELEASE	MAR18/24	K.T









NOTES:

ELECTRICAL:
1. VOLTAGE RATING: 125V
2. CURRENT RATING: 1.25 AMPS PER CONTACT.
3. INSULATING RESISTANCE : 500 MEGAOHMS MINIMUN.
4. DIELECTRIC STRENGTH : 1000 VAC 60Hz, 1MIN.
5. CATEGORY 5e CHARACTERISTIC

FREQUENCY MHZ	NEAR-END CROSSTALK dB,MIN.	RETURN LOSS dB , MIN.	INSERTION LOSS dB,MAX.
1.0	65.0	30.0	0.1
4.0	65.0	30.0	0.1
8.0	64.9	30.0	0.1
10.0	63.0	30.0	0.1
16.0	58.9	30.0	0.2
20.0	57.0	30.0	0.2
25.0	55.0	30.0	0.2
31.25	53.1	30.0	0.2
62.5	47.1	24.1	0.3
100.0	43.0	20.0	0.4

MECHANICAL:
1. SHIELD: STAINLESS STEEL WITH TIN DIP ON SOLDER TABS
2. HOUSING: HIGH TEMP THERMOPLASTIC. UL 94V-0, BLACK
3. INSERT: HIGH TEMP THERMOPLASTIC. UL 94V-0
4. PCB: FR-4
5. CONTACT: PHOSPHOR BRONZE.
   SELECTIVE GOLD PLATING FOR MATING SURFACE,
   50u" MIN. NICKEL UNDERPLATE
   100u" MATTE TIN PLATING ON CONTACT SOLDER TAIL.


ENVIRONMENTAL:
1. OPERATION:-40 °C TO +85°C
2.MATES WITH MODULAR PLUG CONFORMING TO TIA 1096 STANDARD.
3.RECOMMENDED SOLDER PROCESS:
   WAVE SOLDER,PEAR TEMPERATURE 260°C FOR 5~8 SECONDS.

RJ CONNECTOR CONFORMS TIA-1096 STANDARD


AMPHENOL PART NUMBER DESCRIPTION: RJE48-288-6XX1

GOLD PLATING OPTION
1=6µ" GOLD PLATING
2=15µ" MIN GOLD PLATING
3=30µ" MIN GOLD PLATING
4=50µ" MIN GOLD PLATING


LED CODE
SEE SHEET 2



RECOMMENDED PCB LAYTOUT
VIEW FROM COMPONENT SIDE
TOLERANCE: +/-0.05[0.002]



SINGLE COLOR LED



BI-COLOR LED

AMPHENOL CANADA CORP
RoHS COMPLIANT
2011/65/EU RECAST

UNLESS SPECIFIED OTHERWISE	DRAWN	J.CHEN	MAR18/24
PRIMARY UNITS MILLIMETERS	CHECKED	K.TANG	MAR18/24
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.	EAR 15461	
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	
ANGULAR DEGREES ±2°			

Amphenol Canada Corp.
Commercial Products

MODULAR JACK, 1X2 PORTS, 8P8C,
SHIELDED WITHOUT TOP & SIDE TABS,
WITH LED, CAT5e, RoHS COMPLIANT


DWG. NO. P-RJE48-288-6XX1 REV A

CODE ID NO. 03554 | DWG SIZE: X | SCALE: 4:1 | SHEET 1 OF 2


THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL RELEASE	MAR18/24	K.T



RECOMMENDED PANEL CUTOUT



CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)
0	BLOCKED	BLOCKED	9	GREEN	BLOCKED	J	BiC RD/GR	YELLOW
1	YELLOW	GREEN	A	BiC GR/YE	BiC GR/YE	K	YELLOW	BiC GR/OR
2	BLOCKED	GREEN	B	BiC RD/GR	BiC RD/GR	L	BiC GR/YE	RED
3	YELLOW	BLOCKED	C	BiC RD/GR	BiC GR/YE	M	RED	YELLOW
4	GREEN	YELLOW	D	GREEN	BiC GR/YE	N	BiC GR/RD	BiC GR/YE
5	GREEN	GREEN	E	YELLOW	BiC GR/YE	P	GREEN	BiC GR/RD
6	YELLOW	YELLOW	F	BiC GR/YE	YELLOW	R	BiC GR/OR	GREEN
7	RED	GREEN	G	BiC GR/OR	BiC GR/OR	T	RED	RED
8	GREEN	RED	H	BiC GR/YE	GREEN	V	BiC RD/GR	GREEN

EXAMPLE OF ADDITIONAL LED OPTIONS:

RJE48-288-64W1-0X
- ADDITIONAL LED COLOR CODE
- ONLY USED FOR "W" OPTIONS USED IN FIRST LED CODE
- DENOTES ADDITIONAL OPTIONS TO BE USED

CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)
0	DO NOT USE		5	BLOCKED	YELLOW	A	LOWC YE	LOWC YE
1	RED	BLOCKED	6	RED	BiC RD/GR	B	LOWC YE	LOWC GR
2	BiC GR/OR	YELLOW	7	BLOCKED	BiC RD/GR	C	LOWC GR	LOWC YE
3	YELLOW	RED	8	BiC RD/GR	BLOCKED	D	LOWC GR	LOWC GR
4	BLOCKED	RED	9	BiC GR/YE	BLOCKED	M	LOWC RD	LOWC YE
						E	GREEN	ORANGE
						F	ORANGE	GREEN
						G	BiC OR/GR	BiC OR/GR
						H	BiC GR/OR	ORANGE

LED SPECIFICATIONS:
FORWARD VOLTAGE: 1.6 VOLTS TYP.
REVERSE VOLTAGE: 5.0 VOLTS MAX.
LUMINOUS INTENSITY: 0.4 mCd MIN.
(AT IF=2mA)
STORAGE TEMPERATURE: -40° TO 85° C
PLATING ON TAILS: TIN OR TIN/COPPER ALLOY OVER SILVER

LEGEND
BiC=BI-COLOR LED
LOWC=LOW CURRENT LED
YE=YELLOW
GR=GREEN
RE=RED
OR=ORANGE

PRIMARY COLOR FOR BI-COLOR LEDS IN STANDARD ANODE/CATHODE CONFIGURATION IS:
RED-GREEN= RED
RED-YELLOW= RED
GREEN-YELLOW= GREEN
GREEN-ORANGE= GREEN

NOTE:
THE TWO DIGITS PRECEDING THE ADDITIONAL LED CODE MUST BE USED IN THE PART NUMBER, WHEN ORDERING ANY OF THE ADDITIONAL LED OPTIONS.

TRAY PACKING INFORMATION		
CONNECTORS PER TRAY	TRAYS PER CARTON	TOTAL CONNECTORS PER CARTON
20PCS	22PCS	440PCS

AMPHENOL CANADA CORP RoHS COMPLIANT 2011/65/EU RECAST

UNLESS SPECIFIED OTHERWISE	DRAWN	J.CHEN	MAR18/24
PRIMARY UNITS MILLIMETERS	CHECKED	K.TANG	MAR18/24
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.	EAR 15461	
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	
ANGULAR DEGREES ±2°			

Amphenol Canada Corp.
Commercial Products

MODULAR JACK, 1X2 PORTS, 8P8C, SHIELDED WITHOUT TOP & SIDE TABS, WITH LED, CAT5e, RoHS COMPLIANT

DWG. NO. P-RJE48-288-6XX1 REV A

CODE ID NO. 03554 | DWG SIZE: X | SCALE: 4:1 | SHEET 2 OF 2

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.