



Catalog No. TS1025HF

Description: CABLE TIE 20LB NAT NYL 4IN FLM RET

UPC No 5414363059912

Home > Wire & Cable Management > Catamount > Cable ties

Flame Retardant Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length 100mm (3.94 Inches), Width 2.5mm (0.098 Inches), Tensile Strength Rating of 90 Newtons (20 Pounds)

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	20 pounds , 90 newtons

Classifications

Brand Name	Catamount
------------	-----------

Dimensions

Width	0.098 in , 2.5 mm
Length	3.94 in , 100 mm
Bundle Diameter	0.94 in , 24 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000046 Cable tie
Band width	2.5 mm
Length belt/tape/tie	100 mm
Length belt/tape/tie	3.94 inch
Max. bundle diameter	24 mm

by ABB

ETIM	EC000046 Cable tie
Min. holding force	90 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N
Inflammability class of insulation material acc. with UL94	V0