

FUSE STRIP with housing

Rated 48 V



Specifications

Voltage Rating:	48 V DC
Interrupting Rating:	Up to 3000 A
Recommended Environmental Temperature:	-40 °C to +125 °C
Terminals Material:	35 A - 80 A: Zinc alloy 100 A - 500 A: Tin plated copper alloy
Housing Material:	-
Comply With:	UL 248 special purpose fuses - File No. E211637

Description

Use these special purpose fuse strips to protect battery powered fuses up to 48 V. Not intended for automotive or truck applications.

Features & Benefits

- 90° lug and straight fork ensure secure mounting
- Windows in housings show if elements remain intact

Applications

- Battery powered fuses (NOT intended for automotive or truck applications)

Ordering Information

Part Number	Package Size
157.5701.xxx1	50
157.5917.xxx1	50

FUSE STRIP with housing

Rated 48 V

Ratings


Part Number		Current Rating (A)	Typ. Voltage Drop (mV)	Breaking Capacity (VDC/A)	Material Thickness "S" (mm)
a = 11 mm	a = 9 mm*				
157.5701.5351	157.5917.5351	35	125	48/210	0.6
157.5701.5401	—	40	125	48/240	0.6
157.5701.5501	157.5917.5501	50	125	48/300	0.6
157.5701.5631	157.5917.5631	63	125	48/378	0.6
157.5701.5801	157.5917.5801	80	125	48/480	0.6
157.5701.6101	157.5917.6101	100	125	48/600	0.5
157.5701.6121	157.5917.6121	125	125	48/750	0.8
157.5701.6131	—	130	125	48/780	0.8
157.5701.6141	—	135	125	48/810	0.8
157.5701.6151	157.5917.6151	150	125	48/900	0.8
157.5701.6161	157.5917.6161	160	125	48/960	1.0
157.5701.6171	157.5917.6171	175	125	48/1050	1.0
157.5701.6201	157.5917.6201	200	125	48/1200	0.8
157.5701.6231	157.5917.6231	225	125	48/1350	0.5
157.5701.6251	157.5917.6251	250	125	48/1500	0.5
157.5701.6271	157.5917.6281	275	125	48/1650	0.8
157.5701.6301	—	300	125	48/1800	0.8
157.5701.6331	157.5917.6331	325	125	48/1950	0.8
157.5701.6351	157.5917.6351	355	125	48/2130	0.8
157.5701.6401	—	400	125	48/2400	0.8
157.5701.6421	157.5917.6421	425	125	48/2550	1.0
157.5701.6501	157.5917.6501	500	125	48/3000	1.0

Corresponding holder see Section "Fuse Holders."

Dimensions

Dimensions in mm for reference only.


See outline drawing for dimensions and tolerances



FUSE STRIP with housing

Rated 48 V

Time-Current Characteristic Curves



FI = 1.00 (max. operating
current: $1.0 \times I_{\text{rat}}$ at 23°C)

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)	
	35-200	225 - 500
150	3,600 s / –	– / –
160	– / –	60 s / –
220	– / 60 s	
250	0.8 s / 10 s	
400	0.20 / 2 s	