

US-TMF 100 - Marker for terminal blocks



0829260

<https://www.phoenixcontact.com/us/products/0829260>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Card, white, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: latching, snap into flat marker groove, Number of individual labels: 20, text field height: 6.6 mm, text field width: 104 mm

Your advantages

- The cards provide space for including function texts
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- The perforated marking strips are easy to separate and can be easily fitted
- The US-TMF 100 UniSheet markers are suitable for products with a flat marker groove

Commercial data

Item number	0829260
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2119
GTIN	4046356559577
Weight per piece (including packing)	10.4 g
Weight per piece (excluding packing)	9.78 g
Customs tariff number	39204910
Country of origin	DE

US-TMF 100 - Marker for terminal blocks



0829260

<https://www.phoenixcontact.com/us/products/0829260>

Technical data

Product properties

Product type	Terminal marking
Type	flat

Marking

Number of individual labels	20
Number of individual labels per row	1
Identification technology	Thermal transfer for sheets and cards, UV LED technology

Dimensions

Width	104 mm
Height	6.2 mm
Depth	0.3 mm

Text field

Text field width	104 mm
Text field height	6.6 mm

Material specifications

Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
---------------	--------------------------------------

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C ... 30 °C
Recommended humidity (storage/transport)	50 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

US-TMF 100 - Marker for terminal blocks



0829260

<https://www.phoenixcontact.com/us/products/0829260>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-TMF 100 - Marker for terminal blocks



0829260
<https://www.phoenixcontact.com/us/products/0829260>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com