
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – TE Connectivity, SWINDON, UK ALL RIGHTS RESERVED.

COMMERCIALLY CONFIDENTIAL
RESTRICTED CIRCULATION

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	PAPER CHANGE REF. ECR-18-018446	20DEC2018	AFK	LS



PART CODE (1st FIVE DIGITS)	'A' TOP EDGE OF PAPER TO CENTRE OF TUBE	'B' No. OF TUBES AT 'C' PITCH PER PAGE	'C' TUBE POSITION PITCH
HS024	6.40	20	12.7
HS032	6.40	20	12.7
HS048	6.40	20	12.7
HS064	8.46	15	16.93
HS095	12.7	10	25.4
HS127	12.7	10	25.4
HS190	25.4	5	50.8
HS254	25.4	5	50.8
HS381	63.5	2	127

NOTES:–

1. TOLERANCE ON 'C' – ALL SIZES ±0.5mm.
2. EDGES OF TUBE TO BE STRAIGHT/SQUARE TO PAPER EDGE WITHIN 1.0mm TOLERANCE ZONE. SEE DIAGRAM BELOW.



3. NO ACCUMULATIVE PITCH ERROR THROUGH PACK IS ACCEPTABLE.
4. TUBE LENGTH CUT TOLERANCE:– $^{+1}_{-0}$mm.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.5
2 PLC	± 0.5
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL: IRRADIATED POLYOLEFIN TUBE
FINISH: –

DWN AFK 27NOV2012
CHK –
APVD –
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT 0.000000

TE Connectivity

NAME: HSI THERMAL TRANSFER NARROW ASSEMBLY 2:1 PRE TAPED CARRIER –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	0198G	C-1905A0019	–

CUSTOMER DRAWING | SCALE ––– | SHEET 1 OF 1 | REV 3

1470–19 (1/15)

Downloaded from Arrow.com.