



Part Number : [734042270](#)
Product Description : SMB Jack, Right-Angle,
Bulkhead Receptacle, PCB, Through Hole, Brass Body,
Gold (Au) Plated, One Piece Per Bag, 50 Ohms
Series Number : 73404
Status : Active
Product Category : RF / Coaxial Connectors




Documents & Resources

Drawings

- [734042270 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73404
Description	SMB Jack, Right-Angle, Bulkhead Receptacle, PCB, Through Hole, Brass Body, Gold (Au) Plated, One Piece Per Bag, 50 Ohms
Application	RF
Product Name	SMB
Style	PCB
Type	Subminiature
UPC	800756688169

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	4.685/g
Orientation	Right Angle
Packaging Type	Individual Bag
Panel Mount	Yes

Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

This document was generated on Sep 17, 2025