


FO-55111-A

HONEYWELL
PART NUMBER

111SM1

PRODUCT CODE
TYJ0100

REV	DOCUMENT	CHANGED BY	CHECK
10	0038225	PRS 04APR08	BLR



NOTE -
▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .087 MAX DIA ON .375±.002 CENTERS
2-TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.
SR - 8707

REPLACES
-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH		DRAWN		VK		23 OCT 07		Honeywell			
OPERATING FORCE — — — — 7 OZ MAX		CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:		CHECK		RJ		23 OCT 07					
RELEASE FORCE— — — — — 2 OZ MIN		30 VOLTS DC RATING			NO PLACE X ± —		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE SWITCH - BASIC							
DIFFERENTIAL TRAVEL— — — .030 MAX					ONE PLACE .X ± 0.030											
OVERTRAVEL — — — — — .030 MIN		SEA LEVEL 50,000 FT			TWO PLACE .XX ± 0.015											
		INDUCTIVE 3 AMP 2.5 AMP			THREE PLACE .XXX ± 0.005											
		RESISTIVE 5 AMP 5 AMP			FOUR PLACE .XXXX ± —		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		SIZE B		TYPE I		DRAWING NAME 111SM1		REV 10	
		MAXIMUM INRUSH 24 AMP			ANGLES ± —											
		APPROVALS			THIRD ANGLE PROJECTION											
		KEMA, CE 5A, 250V ~ T85 1E4 														
		UL, CSA 5A, 250 VAC ~   BRAND L4														