

Product data sheet

Characteristics

AP6003A

APC NetShelter Basic Rack PDU, Half Height, 100-240V/20A, 220-240V/16A, 14 C13 outlet



Overview

| | |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

Main

| | |
|---------------------------|------------------------------------|
| Color | Black |
| Product or Component Type | PDU |
| PDU Type | Basic |
| Provided Equipment | Installation guide Safety guide |

Complementary

| | |
|-----------------------|--|
| Main Input Voltage | 230 V |
| Height | 20.6 In (523 mm) |
| Width | 2.2 In (56 mm) |
| Output voltage | 100 V 120 V 200 V 208 V 230 V 240 V |
| Depth | 1.9 In (47 mm) |
| Net Weight | 4.14 Lb(US) (1.88 kg) |
| Mounting Location | Side |
| Mounting preference | Lower |
| Input Connection Type | IEC 60320 C20 |
| Mounting Mode | Not rack-mountable |
| Number of rack unit | 0U |
| USB compatible | No |
| Mounting position | Vertical |
| Line Rated Current | 16 A |
| Permissible voltage | 100...240 V |
| Max line current | 20 A |
| Input current limits | 20 A |

| | |
|--------------------------------|------------------|
| Load Capacity | 3300 VA |
| Input Frequency | 50/60 Hz |
| Number of power socket outlets | 14 IEC 60320 C13 |

Environment

| | |
|---------------------------------------|-----------------------------|
| Product Certifications | cUL Listed[RETURN]UL Listed |
| Ambient Air Temperature for Operation | 32...122 °F (0...50 °C) |
| Relative Humidity | 5...95 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | 5...149 °F (-15...65 °C) |
| Storage Relative Humidity | 5...95 % |
| Storage altitude | 0...50000 Ft (0...15240 m) |

Ordering and shipping details

| | |
|------|--------------|
| GTIN | 731304327769 |
|------|--------------|

Packing Units

| | |
|------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 24.09 In (61.2 cm) |
| Package 1 Width | 4.2 In (10.7 cm) |
| Package 1 Length | 4.8 In (12.3 cm) |
| Package weight(Lbs) | 5.62 Lb(US) (2.55 kg) |
| SCC14 | 10731304327766 |

Environmental data

| | |
|--|---|
| Recyclability potential, in % | 45 |
| Total lifecycle Carbon footprint | 1 748 kg CO2 eq. |
| Carbon footprint of the manufacturing phase [A1 to A3] | 0.1837655081 |
| Carbon footprint of the manufacturing phase [A1 to A3] | 0.2 kg CO2 eq. |
| Carbon footprint of the distribution phase [A4] | 0.1837655081 |
| Carbon footprint of the distribution phase [A4] | 0.2 kg CO2 eq. |
| Carbon footprint of the installation phase [A5] | 0 |
| Carbon footprint of the installation phase [A5] | 0 kg CO2 eq. |
| Carbon footprint of the use phase [B2, B3, B4, B6] | 1739.0131979695 |
| RECh free of SVHC | Yes |
| Carbon footprint of the use phase [B2, B3, B4, B6] | 1 739 kg CO2 eq. |
| Lead free | Yes |
| Sustainable packaging | No |
| Carbon footprint of the end-of-life phase [C1 to C4] | 0.1619177952 |
| Carbon footprint of the end-of-life phase [C1 to C4] | 0.2 kg CO2 eq. |
| Environmental Disclosure | Product Environmental Profile |
| Carbon footprint (kg CO2 eq, Total Life cycle) | 1748 |
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No |
| SCIP Number | 1cdb2fed-a06f-4574-913d-8df8e70936b2 |
| RECh Regulation | Free of Substances of Very High Concern above the threshold ↗ |
| EU RoHS Directive | Compliant ↗ |
| Halogen content performance | Product contains halogen above thresholds |
| Circularity Profile | End Of Life Information |

| | |
|------------|--|
| Take-back | No |
| WEEE Label | The product must be disposed on European Union markets following specific waste collection and n |

Contractual warranty

| | |
|----------------------|----|
| Warranty (in months) | 24 |
|----------------------|----|

Product Life Status : **Commercialised**