






NOTES:

1. MATERIAL AND FINISHES:
- HOUSING - BRASS, NICKEL PLATING
 - BODY - BeCu, GOLD PLATING
 - CONTACT PIN - BRASS, GOLD PLATING
 - INSULATOR - PTFE & DELRIN, NATURAL
 - COVER - BRASS, NICKEL PLATING


2. ELECTRICAL:
- A. IMPEDANCE:50 OHM
 - B. FREQUENCY RANGE:DC- 6 GHz

3. MECHANICAL:
- A. DURABILITY:500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -40°C TO + 85°C


4. CRIMP FERRULE WITH .128" HEX



RECOMMENDED
CABLE STRIPPING DIM'S



SCALE 4.000



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

-

REFERENCE
AND
CONFIGURATION LEVEL:

FINISH

DRAWN
STAR

DATE
14-Jul-16

ENGINEER
SUNDE

DATE
14-Jul-16

APPROVED
S.HSIEH

DATE
14-Jul-16

CAD FILE

TITLE
MCX R/A CRIMP PLUG
(FOR RG-178B/U,
196A/U CABLE)

SCALE: 8.0:1.0 SHEET 2 OF 2

DWG SIZE
B

REV
A

Amphenol RF

www.amphenolrf.com

DRAWING NO. 919-389P-51A

ITEM NO. 919-389P-51A

PART NO. 919-389P-51A