
Part Number : 501488100
Product Description : Mizu-P25 Female Crimp Terminal, 2.50mm Pitch, 22-20 AWG, Bag
Series Number : 50148
Status : Not Recommended For New Design
Product Category : Crimp Terminals
Packaging Alternative : 501488000 (Reel)



Documents and Resources

Drawings

501488100_sd.pdf

Specifications

AS-50147-001-001.pdf

522130000-AS-000.pdf

AS-52213-001-001.pdf

AS-52213-001-JP-001.pdf

PK-50148-003-001.pdf

522130000-PS-000.pdf

PS-52213-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Crimp Terminals
Series	50148
Description	Mizu-P25 Female Crimp Terminal, 2.50mm Pitch, 22-20 AWG, Bag
Application	Wire-to-Wire
Product Name	Mizu-P25 Waterproof
UPC	800753347649

Electrical

Voltage - Maximum	125V

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	62.200/mg
Packaging Type	Bag
Termination Interface Style	Crimp or Compression
Terminal Size	1.3
Wire Insulation Diameter	1.40-1.90mm
Wire Size (AWG)	20, 22

Downloaded from Arrow.com.

Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mizu-P25 Waterproof Receptacle Housings	52213

Application Tooling

Global

Description	Part Number
FineAdjust Applicator for 2.5 Mini Waterproof Wire-to-Wire Crimp Terminals, 22-20 AWG	2037024800
PremiumGrade Hand Crimp Tool for 2.50mm Splash Proof Terminals, 22-20 AWG (AVSS and CAVS 0.50-0.30mm)	638118600
Extraction and Activation Tool	638132700

Downloaded from Arrow.com.