


**KDKS 1/PE/35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

**General ordering data**

|                     |                                                                                                                                         |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Version             | Fuse terminal, Screw connection, beige / yellow, 4 mm <sup>2</sup> , 6.3 A, 500 V, Number of connections: 5, Number of levels: 2, TS 35 |
| Order No.           | <a href="#">9528110000</a>                                                                                                              |
| Type                | KDKS 1/PE/35                                                                                                                            |
| GTIN (EAN)          | 4008190898939                                                                                                                           |
| Qty.                | 50 pc(s).                                                                                                                               |
| Alternative product | <a href="#">9532450000</a>                                                                                                              |

Creation date May 23, 2025 12:52:10 PM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 65 mm   | Depth (inches)  | 2.559 inch |
| Height     | 91 mm   | Height (inches) | 3.583 inch |
| Width      | 8 mm    | Width (inches)  | 0.315 inch |
| Net weight | 14.98 g |                 |            |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 100 °C        |

## Material data

|                           |       |        |                |
|---------------------------|-------|--------|----------------|
| Material                  | PA 66 | Colour | beige / yellow |
| UL 94 flammability rating | V-2   |        |                |

## System specifications

|                                     |                                                            |                               |     |
|-------------------------------------|------------------------------------------------------------|-------------------------------|-----|
| Version                             | Screw connection, Fuse isolator, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 3                                                          | Number of levels              | 2   |
| Number of clamping points per level | 2                                                          | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No                                                         | PE connection                 | Yes |
| Rail                                | TS 35                                                      | N-function                    | No  |
| PE function                         | Yes                                                        | PEN function                  | No  |

## 2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

|                                                                                                            |                     |                                                                                                            |                     |
|------------------------------------------------------------------------------------------------------------|---------------------|------------------------------------------------------------------------------------------------------------|---------------------|
| Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, max. | 1 mm <sup>2</sup>   | Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, two clampable wires, min.                                  | 0.5 mm <sup>2</sup> | Wire cross-section, finely stranded, two clampable wires, max.                                             | 1 mm <sup>2</sup>   |

## Additional technical data

|                             |         |                     |                 |
|-----------------------------|---------|---------------------|-----------------|
| Explosion-tested version    | No      | Installation advice | Direct mounting |
| Number of similar terminals | 1       | Open sides          | right           |
| Type of mounting            | Snap-on |                     |                 |

## CSA rating data

|                               |           |                               |        |
|-------------------------------|-----------|-------------------------------|--------|
| Certificate No. (CSA)         | 12400-281 | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 26 AWG    |                               |        |

## Conductors for clamping (additional connection)

|                                                                                             |                   |                                        |                  |
|---------------------------------------------------------------------------------------------|-------------------|----------------------------------------|------------------|
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 4 mm <sup>2</sup> | Connection type, additional connection | Screw connection |
|---------------------------------------------------------------------------------------------|-------------------|----------------------------------------|------------------|

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|                                                                                         |                      |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|---------------------|
| Blade size                                                                              | 0.6 x 3.5 mm         | Clamping range, max.                                                                    | 4 mm <sup>2</sup>   |
| Clamping range, min.                                                                    | 0.33 mm <sup>2</sup> | Clamping screw                                                                          | M 3                 |
| Connection cross-section, stranded, max.                                                | 4 mm <sup>2</sup>    | Connection cross-section, stranded, min.                                                | 1.5 mm <sup>2</sup> |
| Connection direction                                                                    | on side              | Gauge to IEC 60947-1                                                                    | A3                  |
| Number of connections                                                                   | 5                    | Stripping length                                                                        | 9 mm                |
| Tightening torque, max.                                                                 | 1 Nm                 | Tightening torque, min.                                                                 | 0.5 Nm              |
| Torque level with DMS electric screwdriver                                              | 2                    | Type of connection                                                                      | Screw connection    |
| Type of connection 2                                                                    | Screw connection     | Wire connection cross section AWG, max.                                                 | AWG 12              |
| Wire connection cross section AWG, min.                                                 | AWG 22               | Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>   |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>   |
| Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup>  |                                                                                         |                     |

## Display element

|                               |       |
|-------------------------------|-------|
| Type of voltage for indicator | AC/DC |
|-------------------------------|-------|

## Fuse terminals

|                               |              |                                |          |
|-------------------------------|--------------|--------------------------------|----------|
| Cartridge fuse                | G-Si. 5 x 20 | Fuse holder (cartridge holder) | Pivoting |
| Type of voltage for indicator | AC/DC        |                                |          |

## General

|                                         |                              |                                         |        |
|-----------------------------------------|------------------------------|-----------------------------------------|--------|
| Installation advice                     | Direct mounting              | Rail                                    | TS 35  |
| Standards                               | IEC 60947-7-2, IEC 60947-7-3 | Wire connection cross section AWG, max. | AWG 12 |
| Wire connection cross section AWG, min. | AWG 22                       |                                         |        |

## PE rating data

|                          |                              |              |    |
|--------------------------|------------------------------|--------------|----|
| Rated short-time current | 300 A (2.5 mm <sup>2</sup> ) | PEN function | No |
|--------------------------|------------------------------|--------------|----|

## Rating data

|                                              |                   |                                 |                              |
|----------------------------------------------|-------------------|---------------------------------|------------------------------|
| Rated cross-section                          | 4 mm <sup>2</sup> | Rated voltage                   | 500 V                        |
| Rated DC voltage                             | 500 V             | Rated current                   | 6.3 A                        |
| Current at maximum wires                     | 6.3 A             | Standards                       | IEC 60947-7-2, IEC 60947-7-3 |
| Volume resistance according to IEC 60947-7-x | 1 mΩ              | Rated impulse withstand voltage | 6 kV                         |
| Power loss in accordance with IEC 60947-7-x  | 1.02 W            | Pollution severity              | 3                            |

Creation date May 23, 2025 12:52:10 PM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## UL rating data

|                                         |        |                                         |        |
|-----------------------------------------|--------|-----------------------------------------|--------|
| Certificate No. (UR)                    | E60693 | Conductor size Factory wiring max. (UR) | 12 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR)   | 12 AWG |
| Conductor size Field wiring min. (UR)   | 22 AWG |                                         |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000899    | ETIM 7.0    | EC000899    |
| ETIM 8.0    | EC000899    | ETIM 9.0    | EC000899    |
| ETIM 10.0   | EC000899    | ECLASS 9.0  | 27-14-11-16 |
| ECLASS 9.1  | 27-14-11-16 | ECLASS 10.0 | 27-14-11-16 |
| ECLASS 11.0 | 27-14-11-16 | ECLASS 12.0 | 27-14-11-16 |
| ECLASS 13.0 | 27-25-01-13 | ECLASS 14.0 | 27-25-01-13 |
| ECLASS 15.0 | 27-25-01-13 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Important note

|                     |                                                                                  |
|---------------------|----------------------------------------------------------------------------------|
| Product information | The voltage depends on the selected fuse element or the selected indicator light |
|---------------------|----------------------------------------------------------------------------------|

## Approvals

Approvals



|                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/</a> |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E60693     |

## Downloads

|                                             |                                                                                             |
|---------------------------------------------|---------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of Conformity</a><br><a href="#">UKCA declaration of conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                             |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>                                             |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                    |

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                             |
|------------|----------------------------|-------------------------------------------------------------|
| Type       | DEK 5/6.5 MC NE WS         | Version                                                     |
| Order No.  | <a href="#">1609840000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190203429              | Weidmueller, white                                          |
| Qty.       | 900 pc(s).                 |                                                             |

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                             |
|------------|----------------------------|-------------------------------------------------------------|
| Type       | DEK 5/6.5 MC SDR           | Version                                                     |
| Order No.  | <a href="#">1609850000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190456610              | Weidmueller, To customer specification                      |
| Qty.       | 180 pc(s).                 |                                                             |

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                             |
|------------|----------------------------|-------------------------------------------------------------|
| Type       | DEK 5/6.5 PLUS MC SDR      | Version                                                     |
| Order No.  | <a href="#">1046360000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248782062              | Weidmueller, To customer specification                      |
| Qty.       | 180 pc(s).                 |                                                             |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 pc(s).                 |                            |

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 pc(s).                 |                            |

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                             |
|------------|----------------------------|-------------------------------------------------------------|
| Type       | DEK 5/6.5 PLUS MC NE GE    | Version                                                     |
| Order No.  | <a href="#">1364020000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4050118166057              | Weidmueller, yellow                                         |
| Qty.       | 900 pc(s).                 |                                                             |

Creation date May 23, 2025 12:52:10 PM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                             |
|------------|----------------------------|-------------------------------------------------------------|
| Type       | DEK 5/6.5 PLUS MC NE WS    | Version                                                     |
| Order No.  | <a href="#">1046340000</a> | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248782048              | Weidmueller, white                                          |
| Qty.       | 900 pc(s).                 |                                                             |

## 5x20



For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

## General ordering data

|            |                             |                                                    |
|------------|-----------------------------|----------------------------------------------------|
| Type       | G 20/6.30A/F                | Version                                            |
| Order No.  | <a href="#">0431400000</a>  | Miniature fuse, quick-acting, 6.3 A, G-Si. 5 x 20  |
| GTIN (EAN) | 4008190086053               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | G 20/4.00A/F                | Version                                            |
| Order No.  | <a href="#">0431200000</a>  | Miniature fuse, quick-acting, 4 A, G-Si. 5 x 20    |
| GTIN (EAN) | 4008190022983               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | FUSES 250V 6.3A 021506. ... | Version                                            |
| Order No.  | <a href="#">0430300000</a>  | Miniature fuse, quick-acting, 0.1 A, G-Si. 5 x 20  |
| GTIN (EAN) | 4008190077174               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | G 20/1.00A/F                | Version                                            |
| Order No.  | <a href="#">0430700000</a>  | Miniature fuse, quick-acting, 1 A, G-Si. 5 x 20    |
| GTIN (EAN) | 4008190093877               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | G 20/0.20A/F                | Version                                            |
| Order No.  | <a href="#">0430400000</a>  | Miniature fuse, quick-acting, 0.2 A, G-Si. 5 x 20  |
| GTIN (EAN) | 4008190152383               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | G 20/0.25A/F                | Version                                            |
| Order No.  | <a href="#">0430500000</a>  | Miniature fuse, quick-acting, 0.25 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190153991               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | G 20/5.00A/F                | Version                                            |
| Order No.  | <a href="#">0431300000</a>  | Miniature fuse, quick-acting, 5 A, G-Si. 5 x 20    |
| GTIN (EAN) | 4008190185381               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |
| Type       | G 20/1.60A/F                | Version                                            |
| Order No.  | <a href="#">0430800000</a>  | Miniature fuse, quick-acting, 1.6 A, G-Si. 5 x 20  |
| GTIN (EAN) | 4008190031503               |                                                    |
| Qty.       | 10 pc(s).                   |                                                    |

Creation date May 23, 2025 12:52:10 PM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

7

## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

|            |                            |                                                    |
|------------|----------------------------|----------------------------------------------------|
| Type       | G 20/0.63A/F               | Version                                            |
| Order No.  | <a href="#">0439000000</a> | Miniature fuse, quick-acting, 0.63 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190131210              |                                                    |
| Qty.       | 10 pc(s).                  |                                                    |
| Type       | G 20/2.00A/F               | Version                                            |
| Order No.  | <a href="#">0430900000</a> | Miniature fuse, quick-acting, 2 A, G-Si. 5 x 20    |
| GTIN (EAN) | 4008190123567              |                                                    |
| Qty.       | 10 pc(s).                  |                                                    |
| Type       | G 20/3.15A/F               | Version                                            |
| Order No.  | <a href="#">0431100000</a> | Miniature fuse, quick-acting, 3.15 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190012977              |                                                    |
| Qty.       | 10 pc(s).                  |                                                    |
| Type       | G 20/2.50A/F               | Version                                            |
| Order No.  | <a href="#">0431000000</a> | Miniature fuse, quick-acting, 2.5 A, G-Si. 5 x 20  |
| GTIN (EAN) | 4008190085513              |                                                    |
| Qty.       | 10 pc(s).                  |                                                    |
| Type       | G 20/0.50A/F               | Version                                            |
| Order No.  | <a href="#">0430600000</a> | Miniature fuse, quick-acting, 0.5 A, G-Si. 5 x 20  |
| GTIN (EAN) | 4008190046835              |                                                    |
| Qty.       | 10 pc(s).                  |                                                    |

## QB RA



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

|            |                            |                                                                                                                                 |
|------------|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Type       | QB 3 WI RA8 IS             | Version                                                                                                                         |
| Order No.  | <a href="#">0461200000</a> | Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3 mm |
| GTIN (EAN) | 4008190161699              |                                                                                                                                 |
| Qty.       | 50 pc(s).                  |                                                                                                                                 |
| Type       | QB 2 WI RA8 IS             | Version                                                                                                                         |
| Order No.  | <a href="#">0461100000</a> | Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3 mm |
| GTIN (EAN) | 4008190034818              |                                                                                                                                 |
| Qty.       | 50 pc(s).                  |                                                                                                                                 |
| Type       | QB 4 WI RA8 IS             | Version                                                                                                                         |
| Order No.  | <a href="#">0461300000</a> | Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 4, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3 mm |
| GTIN (EAN) | 4008190025373              |                                                                                                                                 |
| Qty.       | 50 pc(s).                  |                                                                                                                                 |

Creation date May 23, 2025 12:52:10 PM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

8



## KDKS 1/PE/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SAK-Series




End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

|            |                            |                                                                      |
|------------|----------------------------|----------------------------------------------------------------------|
| Type       | AP KDKS1                   | Version                                                              |
| Order No.  | <a href="#">9503330000</a> | End plate for terminals, beige, Height: 73.5 mm, Width: 1.5 mm, V-2, |
| GTIN (EAN) | 4008190124212              | Polyamide 66, Snap-on: Yes                                           |
| Qty.       | 20 pc(s).                  |                                                                      |
| Type       | AP KDKS1 DB                | Version                                                              |
| Order No.  | <a href="#">9532470000</a> | End plate for terminals, dark beige, Height: 73.5 mm, Width: 1.5 mm, |
| GTIN (EAN) | 4032248039227              | V-0, Wemid, Snap-on: Yes                                             |
| Qty.       | 20 pc(s).                  |                                                                      |

## Contact sleeve



As accessories for our wide product portfolio of fuse terminal blocks, we also offer the appropriate fuse links. The portfolio includes device protection fuses (miniature fuses) from 5x20 mm up to 10x38 mm, E 14 to E 18 fuse links, as well as automotive fuses and automatic circuit breakers. Gauge rings for the fuse holders round off the overall portfolio.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | VH 25/5/3.4                | Version                    |
| Order No.  | <a href="#">0553300000</a> | SAK Series, Contact sleeve |
| GTIN (EAN) | 4008190095604              |                            |
| Qty.       | 100 pc(s).                 |                            |