

Specifications

Eaton TPC12F-A-CB



Eaton Basic rack PDU, 1U, 5-15P input, 1.44 kW max, 110-125V, 12A, 9 ft cord, Single-phase, Circuit breaker, EMI/RFI filter, TAA compliant, Outlets: (12) 5-15R

General specifications

PRODUCT NAME	Eaton basic PDU
CATALOG NUMBER	TPC12F-A-CB
UPC	786685288932
PRODUCT LENGTH/DEPTH	19 in
PRODUCT HEIGHT	1.7 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	8 lb
WARRANTY	3 year
COMPLIANCES	TAA Compliant
CERTIFICATIONS	UL Listed
GLOBAL CATALOG	TPC12F-A-CB
PRODUCT TYPE	Basic PDU

Product specifications

FORM FACTOR	1U
OUTLET CONTROL	No
PHASE	Single-phase
WATTAGE	1.44 kW max
AMPERAGE RATING	12A
INPUT VOLTAGE	110-125V
INPUT CONNECTION	5-15P
OUTLETS	(12) 5-15R
CORD LENGTH	9 ft
FREQUENCY RATING	50-60 Hz
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Resources

CERTIFICATION REPORTS	Eaton RoHS declaration of conformity: ePDU G3 Eaton RoHS Declaration of Conformity: ePDU G3
DRAWINGS	Eaton PDU TPC12F-A-CB technical drawing Eaton basic PDU TPC12F-A-CB tech drawing
INSTALLATION INSTRUCTIONS	Eaton ePDU G3 troubleshooting guide
MANUALS AND USER GUIDES	Eaton ePDU G3 installation and connectivity quick start Eaton ePDU G3 1U and 2U installation addendum Eaton ePDU G3 replace and configure eNMC module Eaton ePDU G3 operations manual
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TPC12F-A-CB

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

