


PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR
2174821222	MINIFIT SR. M-M 150MM 8 AWG LEAD BK Au	1X8AWG DISC PVC BK UL 10669	150±5	BLACK
2174821223	MINIFIT SR. M-M 225MM 8 AWG LEAD BK Au	1X8AWG DISC PVC BK UL 10669	225±5	BLACK
2174821224	MINIFIT SR. M-M 300MM 8 AWG LEAD BK Au	1X8AWG DISC PVC BK UL 10669	300±5	BLACK
2174821225	MINIFIT SR. M-M 450MM 8 AWG LEAD BK Au	1X8AWG DISC PVC BK UL 10669	450±5	BLACK
2174822222	MINIFIT SR. M-M 150MM 8 AWG LEAD RD Au	1X8AWG DISC PVC RD UL 10669	150±5	RED
2174822223	MINIFIT SR. M-M 225MM 8 AWG LEAD RD Au	1X8AWG DISC PVC RD UL 10669	225±5	RED
2174822224	MINIFIT SR. M-M 300MM 8 AWG LEAD RD Au	1X8AWG DISC PVC RD UL 10669	300±5	RED
2174822225	MINIFIT SR. M-M 450MM 8 AWG LEAD RD Au	1X8AWG DISC PVC RD UL 10669	450±5	RED



ITEM	PART#	DESCRIPTION	QTY	UOM
A	428170032	MiniFit Sr M Crp Term 8awg Sau	2	PC

NOTES:

1. Crimping to be done as per Molex standards.
2. The product specification relies on the terminals & wire spec.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/02/05	A	INITIAL RELEASE	AS20

DOCUMENT STATUS	P1	RELEASE DATE	2021/02/05	14:38:07
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$	DIMENSION UNITS: mm SCALE: NTS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±	CURRENT REV DESC: EC NO: 654859 DRWN: AS20 CHK'D: RDESAI01 APPR: RDESAI01		 SEE TABLE
DIVISIONAL SYMBOLS	INITIAL REVISION: DRWN: AS20 APPR: RDESAI01		PRODUCT CUSTOMER DRAWING	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING: A4-SIZE SERIES: 217482	DOCUMENT NUMBER: 2174821222 DOC TYPE: PSD DOC PART: 000 REVISION: A
		MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET	SHEET NUMBER: 1 OF 1	