







681453635	68145-3635
681453625	68145-3625
MATERIAL NO.	ORDER NO.

NOTES

1. APPLICABLE PCB THICKNESS : 1.6mm
2. RECOMMENDED MOUNTING SCREW : 3.0mm Dia, 6.0mm Length (Min)
TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE : 4.0Kgf MAX.)
3. MATING CONNECTOR : 35564-2015, 35563-1615

5	040 TERMINAL S (LONG TAIL)	104588-9103	C2680 (648971096)	-	-	18
4	040 TERMINAL L (LONG TAIL)	104588-9003	C2680 (648971095)	-	-	18
3	040 TERMINAL S (SHORT TAIL)	104588-9203	C2680 (648971096)	-	18	-
2	040 TERMINAL L (SHORT TAIL)	104588-9303	C2680 (648971095)	-	18	-
1	040 HEADER 36P	68145-3685	PBT-GF30 (899922201)	GRAY	1	1
NO.	DECRPTION	P/NUMBER	MATERIAL	COLOR	Q'TY	

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
▽ = 0 ▽ = 0 ▽ = 0		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
		mm		1:1											
▽ = 0 ▽ = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 602957 DRWN: JWKIM02 2018/08/16 CHK'D: JHJANG 2018/08/20 APPR: JHJANG 2018/08/20				040 HEADER ASSY 36P					
		ANGULAR TOL ± °													
▽ = 0 ▽ = 0		4 PLACES		±		INITIAL REVISION: DRWN: JWKIM02 2018/07/30 APPR: JHJANG 2018/08/20				PRODUCT CUSTOMER DRAWING					
		3 PLACES		±											
▽ = 0 ▽ = 0		2 PLACES		± 0.2		DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
		1 PLACE		± 0.3											
▽ = 0 ■ = 0		0 PLACES		±		681453635				PSD		000		C	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
▽ = 0 ▽ = 0		THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		68145		681453635		GENERAL		1 OF 1	