





| REVISIONS |     |                              |           |     |      |
|-----------|-----|------------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION                  | DATE      | DWN | APVD |
| N1        |     | REVISED AS PER ECN-23-216911 | 09JUN2023 | MT  | GL   |

|          |     |            |         |                                   |             |
|----------|-----|------------|---------|-----------------------------------|-------------|
| OBSOLETE | 35  | 26 AWG     | 1000±25 | 4000 <sup>+80</sup> <sub>-0</sub> | 1-2053453-3 |
| OBSOLETE | 35  | 26 AWG     | 1000±25 | 3500 <sup>+80</sup> <sub>-0</sub> | 1-2053453-2 |
| OBSOLETE | 35  | 26 AWG     | 1000±25 | 3000 <sup>+80</sup> <sub>-0</sub> | 1-2053453-1 |
| OBSOLETE | 35  | 26 AWG     | 1000±25 | 4500 <sup>+80</sup> <sub>-0</sub> | 1-2053453-0 |
|          | 50  | 30 AWG     | 1000±25 | 1500 <sup>+50</sup> <sub>-0</sub> | 2053453-8   |
|          | 50  | 30 AWG     | 1000±25 | 2500 <sup>+80</sup> <sub>-0</sub> | 2053453-7   |
| OBSOLETE | 35  | 26 AWG     | 1000±25 | 5000 <sup>+80</sup> <sub>-0</sub> | 2053453-6   |
|          | 50  | 28 AWG     | 1000±25 | 4000 <sup>+80</sup> <sub>-0</sub> | 2053453-5   |
|          | 50  | 30 AWG     | 1000±25 | 3000 <sup>+80</sup> <sub>-0</sub> | 2053453-4   |
|          | 50  | 30 AWG     | 1000±25 | 2000 <sup>+80</sup> <sub>-0</sub> | 2053453-3   |
|          | 50  | 30 AWG     | 500±25  | 1000 <sup>+50</sup> <sub>-0</sub> | 2053453-2   |
|          | 50  | 30 AWG     | 250±25  | 500 <sup>+50</sup> <sub>-0</sub>  | 2053453-1   |
| 9        | "X" | CABLE GAGE | L2      | L1                                | PART NO     |


|                                        |       |                                        |                                |                                          |              |
|----------------------------------------|-------|----------------------------------------|--------------------------------|------------------------------------------|--------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |       |                                        | DWN<br>B DU<br>31OCT2008       | TE Connectivity Ltd.                     |              |
|                                        |       |                                        | CHK<br>J. ELLISON<br>31OCT2008 |                                          |              |
| DIMENSIONS:<br>mm                      |       | TOLERANCES UNLESS OTHERWISE SPECIFIED: |                                | NAME<br>CABLE ASSEMBLY, QSFP TO [4] SFP+ |              |
|                                        | 0 PLC | ±                                      | -                              | PRODUCT SPEC                             |              |
|                                        | 1 PLC | ±                                      | -                              | APPLICATION SPEC                         |              |
|                                        | 2 PLC | ±                                      | -                              | SIZE                                     |              |
|                                        | 3 PLC | ±                                      | -                              | CAGE CODE                                |              |
|                                        | 4 PLC | ±                                      | -                              | DRAWING NO                               |              |
| MATERIAL                               |       | FINISH                                 |                                | RESTRICTED TO                            |              |
| -                                      |       | -                                      |                                | -                                        |              |
| WEIGHT                                 |       |                                        | 0                              | A1 00779                                 |              |
| CUSTOMER DRAWING                       |       |                                        | SCALE                          | 1:1                                      | SHEET 1 OF 2 |
|                                        |       |                                        |                                |                                          | REV N1       |

1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS  
(MEASURED DIFFERENTIALLY)

2 LABEL INFORMATION:



3 LABEL INFORMATION:



4 LABEL INFORMATION:



5. CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY, OPENS, SHORTS AND  
PROPER EEPROM PROGRAM.

6. SEE SHEET 2 FOR WIRING DIAGRAM.

7. PRODUCT AND PROCESSING MEETS THE REQUIREMENTS OF  
TE STANDARD TEC-138-702.

8 SERIAL NUMBER BEGINS WITH 001 AT THE BEGINNING OF EACH WEEK.

9 SEE TABLE FOR HEAT SHRINK TUBE LENGTH.



D

C

B


A

D

C

B

A



SFP+  
P2

SFP+  
P4

SFP+  
P3

SFP+  
P1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL  
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ± —  
1. PLC ± —  
2. PLC ± —  
3. PLC ± —  
4. PLC ± —  
ANGLES ± —

FINISH  
—

DWN  
DU  
31OCT2008

CHK  
J. ELLISON  
31OCT2008

APVD  
J. ELLISON  
31OCT2008

NAME  
PRODUCT SPEC  
APPLICATION SPEC  
WEIGHT  
—

SIZE  
A1  
CAGE CODE  
00779  
DRAWING NO  
2053453  
RESTRICTED TO  
—

TE Connectivity Ltd.

CABLE ASSEMBLY, QSFP TO (4) SFP+

SCALE  
1:1

SHEET  
2

OF  
2

REV  
N1