


High Speed PT IGBT

POWER MOS 8® is a high speed Punch-Through switch-mode IGBT. Low E_{off} is achieved through leading technology silicon design and lifetime control processes. A reduced E_{off} - $V_{CE(ON)}$ tradeoff results in superior efficiency compared to other IGBT technologies. Low gate charge and a greatly reduced ratio of C_{res}/C_{ies} provide excellent noise immunity, short delay times and simple gate drive. The intrinsic chip gate resistance and capacitance of the poly-silicone gate structure help control di/dt during switching, resulting in low EMI, even when switching at high frequency.

APT102GA60B2



APT102GA60L

Single die IGBT



FEATURES

- Fast switching with low EMI
- Very Low E_{off} for maximum efficiency
- Ultra low C_{res} for improved noise immunity
- Low conduction loss
- Low gate charge
- Increased intrinsic gate resistance for low EMI
- RoHS compliant 

TYPICAL APPLICATIONS

- ZVS phase shifted and other full bridge
- Half bridge
- High power PFC boost
- Welding
- UPS, solar, and other inverters
- High frequency, high efficiency industrial

Absolute Maximum Ratings

Symbol	Parameter	Ratings	Unit
V_{CES}	Collector Emitter Voltage	600	V
I_{C1}	Continuous Collector Current @ $T_c = 25^\circ\text{C}$ ¹	183	A
I_{C2}	Continuous Collector Current @ $T_c = 100^\circ\text{C}$	102	
I_{CM}	Pulsed Collector Current ²	307	
V_{GE}	Gate-Emitter Voltage ³	± 30	V
P_D	Total Power Dissipation @ $T_c = 25^\circ\text{C}$	780	W
SSOA	Switching Safe Operating Area @ $T_j = 150^\circ\text{C}$	307A @ 600V	
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to 150	$^\circ\text{C}$
T_L	Lead Temperature for Soldering: 0.063" from Case for 10 Seconds	300	

Static Characteristics

 $T_J = 25^\circ\text{C}$ unless otherwise specified

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
$V_{BR(CES)}$	Collector-Emitter Breakdown Voltage	$V_{GE} = 0V, I_C = 250\mu\text{A}$	600			V
$V_{CE(on)}$	Collector-Emitter On Voltage	$V_{GE} = 15V, I_C = 62A$ $T_J = 25^\circ\text{C}$ $T_J = 125^\circ\text{C}$		2.0 1.9	2.5	
$V_{GE(th)}$	Gate Emitter Threshold Voltage	$V_{GE} = V_{CE}, I_C = 2.5mA$	3	4.5	6	
I_{CES}	Zero Gate Voltage Collector Current	$V_{CE} = 600V, V_{GE} = 0V$ $T_J = 25^\circ\text{C}$ $T_J = 125^\circ\text{C}$			1000 5000	μA
I_{GES}	Gate-Emitter Leakage Current	$V_{GS} = \pm 30V$			± 100	nA

Thermal and Mechanical Characteristics

Symbol	Characteristic	Min	Typ	Max	Unit
$R_{\theta JC}$	Junction to Case Thermal Resistance	-	-	0.16	$^\circ\text{C/W}$
W_T	Package Weight	-	5.9	-	g
Torque	Mounting Torque (TO-247 Package), 4-40 or M3 screw			10	in·lbf

Dynamic Characteristics

$T_J = 25^{\circ}\text{C}$ unless otherwise specified

APT102GA60B2_L

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
C_{ies}	Input Capacitance	Capacitance $V_{GE} = 0\text{V}$, $V_{CE} = 25\text{V}$ $f = 1\text{MHz}$		8170		pF
C_{oes}	Output Capacitance			630		
C_{res}	Reverse Transfer Capacitance			78		
Q_g^4	Total Gate Charge	Gate Charge $V_{GE} = 15\text{V}$ $V_{CE} = 300\text{V}$ $I_C = 62\text{A}$		294		nC
Q_{ge}	Gate-Emitter Charge			56		
Q_{gc}	Gate- Collector Charge			106		
SSOA	Switching Safe Operating Area	$T_J = 150^{\circ}\text{C}$, $R_G = 4.7\Omega^5$, $V_{GE} = 15\text{V}$, $L = 100\mu\text{H}$, $V_{CE} = 600\text{V}$	307			A
$t_{d(on)}$	Turn-On Delay Time	Inductive Switching (25°C) IGBT and Diode $V_{CC} = 400\text{V}$ $V_{GE} = 15\text{V}$ $I_C = 62\text{A}$ $R_G = 4.7\Omega^5$ $T_J = +25^{\circ}\text{C}$		28		ns
t_r	Current Rise Time			37		
$t_{d(off)}$	Turn-Off Delay Time			212		
t_f	Current Fall Time			101		
E_{on2}	Turn-On Switching Energy			1354		μJ
E_{off}^7	Turn-Off Switching Energy			1614		
$t_{d(on)}$	Turn-On Delay Time	Inductive Switching (125°C) IGBT and Diode $V_{CC} = 400\text{V}$ $V_{GE} = 15\text{V}$ $I_C = 62\text{A}$ $R_G = 4.7\Omega^5$ $T_J = +125^{\circ}\text{C}$		27		ns
t_r	Current Rise Time			37		
$t_{d(off)}$	Turn-Off Delay Time			247		
t_f	Current Fall Time			142		
E_{on2}	Turn-On Switching Energy			2106		μJ
E_{off}^7	Turn-Off Switching Energy			1852		

1 Continuous current limited by package lead temperature.

2 Repetitive Rating: Pulse width and case temperature limited by maximum junction temperature.

3 Pulse test: Pulse Width $< 380\mu\text{s}$, duty cycle $< 2\%$.

4 See Mil-Std-750 Method 3471.

5 R_G is external gate resistance, not including internal gate resistance or gate driver impedance. (MIC4452)

6 E_{on2} is the clamped inductive turn on energy that includes a commutating diode reverse recovery current in the IGBT turn on energy loss. A combi device is used for the clamping diode.

7 E_{off} is the clamped inductive turn-off energy measured in accordance with JEDEC standard JESD24-1.

Microsemi reserves the right to change, without notice, the specifications and information contained herein.

Typical Performance Curves

APT102GA60B2_L




FIGURE 1, Output Characteristics ($T_J = 25^\circ\text{C}$)




FIGURE 3, Transfer Characteristics




FIGURE 5, On State Voltage vs Gate-to-Emitter Voltage




FIGURE 7, Threshold Voltage vs Junction Temperature




FIGURE 2, Output Characteristics ($T_J = 25^\circ\text{C}$)




FIGURE 4, Gate charge




FIGURE 6, On State Voltage vs Junction Temperature




FIGURE 8, DC Collector Current vs Case Temperature

Typical Performance Curves

APT102GA60B2_L




FIGURE 9, Turn-On Delay Time vs Collector Current




FIGURE 11, Current Rise Time vs Collector Current




FIGURE 13, Turn-On Energy Loss vs Collector Current




FIGURE 10, Turn-Off Delay Time vs Collector Current




FIGURE 12, Current Fall Time vs Collector Current




FIGURE 14, Turn-Off Energy Loss vs Collector Current




FIGURE 15, Switching Energy Losses vs Gate Resistance




FIGURE 16, Switching Energy Losses vs Junction Temperature

Typical Performance Curves

APT102GA60B2_L




FIGURE 17, Capacitance vs Collector-To-Emitter Voltage




FIGURE 18, Minimum Switching Safe Operating Area




Figure 19, Maximum Effective Transient Thermal Impedance, Junction-To-Case vs Pulse Duration




Figure 20, Inductive Switching Test Circuit




Figure 21, Turn-on Switching Waveforms and Definitions






Figure 22, Turn-off Switching Waveforms and Definitions

T-MAX™ (B2) Package Outline



These dimensions are equal to the TO-247 without the mounting hole.
Dimensions in Millimeters and (Inches)

TO-264 (L) Package Outline



Dimensions in Millimeters and (Inches)