

LED Driver

Outdoor 100W Driver

SL-LU262A001US (UL Type TL)

SL-LU262A002US (UL Class P)



Constant Current LED Driver

High Efficiency Constant Current LED Driver With Active Power Factor Correction

Features & Benefits

- Output Current Range: 2600 mA Fixed
- Output Voltage Range: 30 ~ 39 Vdc
- Output Power Range: Max. 100 W
- Dimming Control: 0 - 10 Vdc
- Input Voltage: 120 ~ 277 Vac, 50 / 60 Hz
- Safety: UL / cUL (UL 8750, CSA C22.2 No.223-M91)
- EMI: FCC Part 15 Class B
- Protections: Short Circuit, Open Load Voltage, Over Temperature
- t_a Range: -40 ~ +70 °C
- Expected lifetime: 50,000 hours at $t_c < 75$ °C
- Environmental Compliance: RoHS
- Long lasting & high reliability
- Metal housing

Applications

- LED Street/Tunnel Lighting and Outdoor LED Lighting



SAMSUNG

Table of Contents

1.	Characteristics	-----	3
2.	Typical Characteristics Graphs	-----	5
3.	Protection	-----	7
4.	Dimming Specification	-----	7
5.	Reliability& standard	-----	8
6.	Outline Drawing & Dimension	-----	9
7.	Label Structure	-----	11
8.	Packing Structure	-----	11
9.	Precautions in Handling & Use	-----	11


1. Characteristics

Article	Symbol	Specification			Unit	Note
		Min.	Typ.	Max.		
INPUT SPECIFICATIONS						
Nominal Voltage	Vin	120~277			Vac	
Voltage Range		108		305		
Nominal Frequency	Fin	50 / 60			Hz	
Frequency Range		47		63		
Input Power	Pin			120	W	Vin = 120 ~ 277Vac, 100% load
Input Current	Iin			1.2	A	Vin = 120Vac, 100% load
				0.55	A	Vin = 277Vac, 100% load
Total Harmonic Distortion	THD			20	%	Vin = 120 ~ 277Vac, 80 ~ 100% load
Power Factor	PF	0.9			-	
Efficiency	η	84	86		%	Vin = 120Vac, 100% load
		85	87			Vin = 277Vac, 100% load
In-rush Current				30	A _{pk}	Vin = 300Vac, 25°C Cold start Twidth=300us measured at %50Ipk
Leakage Current				0.7	mA	Vin = 300Vac
OUTPUT SPECIFICATIONS						
Output Voltage	Vo	30		39	Vdc	
Max. Voltage	Vp			48		
Output Current	Io		2600		mA	Tolerance = ±5%Io
Output Peak Current	Ip			3730	mA	Vin = 120~277Vac, 100% load
Output Ripple Current	Iripple			1000	mA	Vin = 120~277Vac, 100% load
Line/Load Regulation		-5		+5	%	Vin = 120 ~ 277Vac
Temperature Drift		-2		+2	%	Vin = 120Vac, Vout = 34Vdc, Run after 3hours
Aux. Output Voltage	Vaux		12		Vdc	
Aux. Output Current	Iaux		100	150	mA	
Nominal Power	Po			100	W	
Turn-on Delay Time	Td			1.5	s	Vin = 120Vac, 100% load


Article	Symbol	Specification			Unit	Note
		Min.	Typ.	Max.		
DIMMING SPECIFICATIONS						
Dimming Rangel		0		100	%	See 4)Dimming Specification section
Dim. Off			0.93		Vdc	± 0.05Vdc
Dim. Min			1			10%Io
Dim. On			1.35			± 0.1Vdc
Dim. Max		8		10		100%Io
I _{SOURCE}		0		0.5	mA	
ENVIRONMENTAL SPECIFICATIONS						
Ambient Temperature	t _a	-40		70	°C	
Case Temperature	t _c			90		
Storage Temperature	t _s	-40		85		
Ambient Humidity		20		95	%	Not condensing
Storage Humidity		10		95	%	Not condensing
Lightning Surge	L / N	±4			kV	IEC/EN 61000-4-5
	L-N / F.G	±6				
IP Rating			67		-	
Expected Lifetime (e-cap)		50,000			h	At t _c < 75°C
MTBF			300,000			At t _a = 25°C
Dimensions	L x W x H		187 x 67.5 x 40		mm	
Net Weight			870		g	

2. Typical Characteristics Graphs


a) PF vs. Load




b) THD vs. Load




c) Efficiency vs. Load




d) Ta vs. Load



e) Input Voltage vs. Load



f) Lifetime vs. tc




3. Protection

Protection Specification	Protection Mode	Condition
Output Short Protection	Auto-Recovery	(1) AC turn on then output short (2) Output short then AC turn on
Output Open Protection	Clamp Open Load Voltage under 48Vdc	(1) AC turn on then output open (2) Output open then AC turn on
Output Temperature Protection	Current Reduction to %50I _o	V _{in} = Rated Voltage, t _c point : 110°C, 100% load

4. Dimming Specification

The unit has Analog Dimming (AD) function, using 0-10 Vdc.

The typical dimming curve is shown below.



5. Reliability& Standards

a) Safety and EMC

International Standard	Certification
UL Safety Standards (Class 2 Output)	UL 8750
	CAN/CSA-C22.2 No. 250.13-12 CAN/CSA-C22.2 No.107.1-01
Electro Magnetic Compatibility	FCC Part 15 Class B
IEC/EN Safety Standards for LED Lighting	IEC/EN 61347-1 IEC/EN 61347-2-13
Conducted and Radiated Emission Test	IEC/EN 55015
Harmonic current emissions: Class C	IEC/EN 61000-3-2
Voltage Fluctuations and Flicker	IEC/EN 61000-3-3
Electrostatic Discharge (ESD): Contact $\pm 8\text{kV}$, Air $\pm 15\text{kV}$	IEC/EN 61000-4-2
Radio-frequency Electromagnetic Fields	IEC/EN 61000-4-3
Electrical Fast Transients (EFT)	IEC/EN 61000-4-4
Surge: Differential mode $\pm 4\text{kV}$, Common mode $\pm 6\text{kV}$	IEC/EN 61000-4-5
Injected Currents, Conducted disturbances induced by Radio-Frequency fields	IEC/EN 61000-4-6
Power Frequency Magnetic Fields	IEC/EN 61000-4-8
Voltage Dips and Short Interruptions	IEC/EN 61000-4-11

b) Wiring

Input harness

Wire	Symbol	Color	Description	Cable
1	Live	Black	AC Input	SJTW PVC, 18AWG
2	Neutral	White		
3	F.G	Yellow-Green	Protective Ground	

Output harness

Wire	Symbol	Color	Description	Cable
1	V+	Red	Positive(Anode) LED Output(LED+)	SJTW PVC, 18AWG
2	V-	Blue	Negative(Cathode) LED Output(LED-)	

Output harness(DIM - Type TL)

Wire	Symbol	Color	Description	Cable
1	DIM+	Purple	External 0-10V Dimming Input	UL 2517, 22AWG
2	12V	Yellow	External 12V Power Supply Output	
3	DIM-	Gray	Dimming Signal Ground	

Output harness(DIM - Class P)

Wire	Symbol	Color	Description	Cable
1	DIM+	Purple	External 0-10V Dimming Input	UL 21996, 18AWG
2	12V	Yellow	External 12V Power Supply Output	
3	DIM-	Gray	Dimming Signal Ground	

7. Driver Label

SL-LU262A001US

INPUT ● AC/L BLACK ● AC/N WHITE ● YE-GN	SAMSUNG	LED Driver Model: SL- LU262A001US Input Voltage :120-277 Vac 50/60Hz Input Current :1.2A Output Voltage :30-39Vdc Output Current :2600mA Output Power:101W	  IP67 RoHS Aux Output: 12V---150mA Suitable for use in Dry & Damp Locations Type TL 90/72°C MADE IN CHINA	DIM 12V Yellow 0-10V Purple NEG Gray OUTPUT V-: BLUE ● V+: RED ●

SL-LU262A002US

INPUT ● AC/L BLACK ● AC/N WHITE ● YE-GN	SAMSUNG	LED Driver Model: SL- LU262A002US Input Voltage :120-277 Vac 50/60Hz Input Current :1.2A Output Voltage :30-39Vdc Output Current :2600mA Output Power:101W Aux Output: 12V---150mA	  IP67 RoHS Suitable for use in Dry & Damp Locations For Connections Use Wire Rated for at Least 90°C(194°F) Type HL Class P MADE IN CHINA	DIM 12V Yellow 0-10V Purple NEG Gray OUTPUT V-: BLUE ● V+: RED ●

8. Packing Structure

Packing material	Driver Quantity	Dimension (mm)		
		Length	Width	Height
Outer Box	10	340	200	265
Pallet	320	850	820	1185

9. Precautions in Handling & Use

- To prevent the LED Driver from any defect, please handle and store it with care
 - Do not drop or give shock
 - Do not store in very humid location or at extreme temperature
 - Do not open or disassemble the product
- Static electricity or surge voltage may damage the components inside LED Driver, as such please observe proper anti-electrostatic working process
 - People handling the Driver should be well grounded (e.g. using ESD wrist band) and wear anti-static working clothes and gloves
 - All related devices and instruments in the production line should be well grounded (e.g. working table, measuring equipment, assembly jigs)
- Observe the correct polarity of output terminal
- Avoid input voltage exceeds the maximum rating, which will cause damage to the circuit and result in malfunction

SAMSUNG

Legal and additional information.

About Samsung Electronics Co., Ltd.

Samsung Electronics Co., Ltd inspires the world and shapes the future with transformative ideas and technologies.

The company is redefining the worlds of TVs, smartphones, wearable devices, tablets, digital appliances, network systems, and semiconductor and LED solutions. For the latest news, please visit the Samsung Newsroom at <http://news.samsung.com>.

Copyright © 2018 Samsung Electronics Co., Ltd. All rights reserved.

Samsung Electronics reserves the right to modify, at its sole discretion, the design, packaging, specifications and features shown herein without notice at any time.

Samsung Electronics Co., Ltd.
Samsung-ro, Giheung-gu
Yongin-si, Gyeonggi-do, 17113
KOREA
www.samsungled.com

SAMSUNG