



a) Part as supplied

224K012-*—G02



b) Part after unrestricted recovery.



DIMENSIONS (in millimetres).

	H		J		P	R	JO	T	U	JW	HW
Part	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±20%	±20%
Number	a	b	a	b	b	b	b	b	b	b	b
224K012-*—G02	24	14	16	3.3	33	25	15	1.5	0.8	1.8	0.8
	#		#								

This is an overexpanded variant
Modified dimensions are shown thus:- #

Copyright (!)


The copyright in this drawing is the property of Tyco Electronics UK Ltd. The drawing is issued on the condition that it is not copied, reproduced or disclosed to a third party, either in whole or in part without the prior written consent of Tyco Electronics UK Ltd.

Drawn A.LILLEY. Checked *[Signature]* Issue 3 Date November 2000 Conforms to ISO Recommendations

Approval
Design *[Signature]*

MKTG. *[Signature]* Q.A. *[Signature]*

3rd Angle Projection
Not to Scale



Iss.	Date	E.C.R. No.	Details of Change
2	July 1989	5507	H & J min was 18
3	November 2000	****	Redrawn

Ordering Information

224K012-*G02/**-0			
	↑	↑	↑
			Adhesive Slash Number (if required see compatibility chart)
			Modification number
			Material Dash Number (see compatibility chart)
			Base Part Number

COMPATIBILITY CHART

MATERIAL DASH NUMBER	MATERIAL DESCRIPTION	COATING SLASH NUMBER
-3	POLYOLEFIN, SEMI-RIGID	/42, /86
-4	POLYOLEFIN, FLEXIBLE	/42, /86
-25	ELASTOMER, FLUID RESISTANT	/86, /225
-130	POLYOLEFIN, COMMERCIAL FLEXIBLE	/42, /86

AS SUPPLIED DIMENSIONS ARE FOR UNCOATED PARTS,
WHEN COATING IS ADDED, ENTRY DIAMETERS WILL REDUCE BY 1.5mm MAX.

Raychem Wire & Harness
a Division of Tyco Electronics
Faraday Road,
Swindon, Wiltshire, England. SN3 5JA
Telephone: (01793) 528171 Fax: 572516

Raychem Wire & Harness
a Division of Tyco Electronics
300, Constitution Drive, Menlo Park,
California 94025-1164, USA
Telephone (650) 361-3333 Fax: (650) 361-5579