

Product data sheet

Specifications



APC Smart-UPS On-Line, 5kVA,
Rackmount 3U, 208V, 4x C13+4x
C19 IEC outlets, Network
Card+SmartSlot, Extended runtime,
W/ rail kit

SRT5KRMXLT-IEC

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	240 V
Main Output Voltage	208 V
Other Output Voltage	240 V
Rated power in W	4800 W
rated power in VA	5000 VA
Input Connection Type	NEMA L6-30P
output connection type	4 IEC 60320 C13 2 IEC Jumpers 4 IEC 60320 C19
Number of rack unit	3U
Cable length	3.05 m
Number of cables	1
Provided equipment	Documentation CD Rack mounting hardware Rack mounting brackets Rack mounting support rails User manual USB cable Warranty card Web/SNMP management card
Range of product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery type	Lead-acid battery
Battery voltage	192 V
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery recharge time	1.5 h
Number of battery replacement quantity	1
Battery life	3...5 year(s)
Replacement battery	APCRBC140 
Battery charger power	556 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
UPS type	Double conversion online

Physical

Colour	Black
Height	13 cm
Width	43.2 cm
Depth	71.9 cm
Net weight	55.79 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

Input

Input voltage limits	100...275 V adjustable (half load)
Network frequency	40...70 Hz auto-sensing

Output

Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2 %
Maximum configurable power in VA	5000 VA
Maximum configurable power in W	4800 W
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	ENERGY STAR V2.0 (USA)
------------------------	------------------------

Environmental

Acoustic level	55 dBA
Heat dissipation	1047 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0...15240 m
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency power off	Yes
Free slots	1
Preinstalled device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rate	480 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	96 cm
Package 1 Length	61 cm
Package 1 Weight	68.04 kg

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	8949
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	409c68a1-39a6-4e5f-b080-12befe783ad8
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Energy efficiency	
Energy Efficiency Optimized	Energy efficient product
 ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative









