







NOTE
1. CONTACT PLATING
GOLD (0.2μm) ON MATING AREA AND
TERMINATION AREA ALL OVER NICKEL.

2. PART NO.
PCS-E () PM ()

PART NO.	CABLE CHARACTERISTICS	
PCS-E () PMK	FOR DISCRETE WIRE	#30AWG (7/0.1)
	O. D. : 0.65~0.8	
PCS-E () PMJ	FOR DISCRETE WIRE	#28AWG (7/0.127)
	O. D. : 0.65~0.8mm	#30AWG (1/0.254)
PCS-E () PMD	FOR DISCRETE WIRE	#30AWG (7/0.1)
	O. D. : 0.5~0.65mm	
PCS-E () PMC	FOR DISCRETE WIRE	#28AWG (7/0.127)
	O. D. : 0.5~0.65mm	#30AWG (1/0.254)
PCS-E () PMB	FOR FLAT CABLE	#30AWG (7/0.1)
	THICKNESS: 1mm MAX.	
PCS-E () PMA	FOR DISCRETE WIRE	#28AWG (7/0.127)
	O. D. : 0.8~1.0mm	#30AWG (1/0.254)
PCS-E () PM	FOR FLAT CABLE	#28AWG (7/0.127)
	THICKNESS: 1mm MAX.	#30AWG (1/0.254)

6	CABLE COVER	PBT (GF)	2	UL94V-0 BLACK
5	SUPPORTER	PBT (GF)	2	UL94V-0 BLACK
4	INSULATOR	PBT (GF)	1	UL94V-0 BLACK
3	SHELL	ZINC ALLOY	1	NICKEL PLATING
2	CONTACT B	PHOSPHOR BRONZE	NO. OF POS./2	NOTE #1
1	CONTACT A	PHOSPHOR BRONZE	NO. OF POS./2	NOTE #1

LTR.	DATE	BY	REV.	DESCRIPTION	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
	JUL.3.1998		2/1	SCALE	UNIT	3RD. A. P				
	APP. DATE&REV.				mm (INCH)					
DR.	DE.	CHK.	CHK.	APP.						
Y. OHKI	Y. OHKI	K. SATO	Y. HIRAI	H. MIYAKI						

PCS-E68PM ()	68	63.9	57.9	46.28	1.27x33=41.91	52.1	52.1	PCS-E68PM
PCS-E50PM ()	50	52.5	46.5	34.85	1.27x24=30.48	40.7	40.7	PCS-E50PM
PCS-E36PM ()	36	43.6	37.6	25.96	1.27x17=21.59	31.8	31.8	PCS-E36PM
PCS-E28PM ()	28	38.5	32.5	20.88	1.27x13=16.51	26.7	26.7	PCS-E28PM
PCS-E20PM ()	20	33.4	27.4	15.8	1.27x 9=11.43	21.6	21.65	PCS-E20PM
PART NO.	N (NO. OF POS.)	A	B	C	D	E	F	MARKING (P/N)

DIMENSIONS

HONDA TSUSHIN KOGYO CO., LTD.

NAME
PCS-E TYPE MALE
CONNECTOR (PANEL MOUNT)

PART NO.
PCS-E () PM ()