

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

YZ-2R5556T

AWG8551

YZ-2R5556T

PAGE 1 OF 1

M

DRAWING
NUMBER

B

ISSUE

X115108-YZ

REPLACES

RELEASE NO. ECO-0005292

REVISIONS

A 0015138
SPK
29 AUG 05

CHECK

29 AUG 05

RJ

CHECK

06 MAY 04

AK

CHECK


06 MAY 04

KR

RASTER

FO-52848-A

DRAWN




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE-----8-15 OZ

RELEASE FORCE-----4 OZ MIN

DIFFERENTIAL TRAVEL-----.0004-.0025

OVERTRAVEL-----.005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

L96

15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

-L288-
-L306-
-L315-



EN 05
EC



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.07/03
ONE PLACE	X.X	0.4/.015	X.X	0.38/.015
TWO PLACES	X.XX	0.15/.005	X.XX	0.13/.005
THREE PLACES	X.XXX		X.XXX	
ANGLES				

DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY

WEIGHT .065 LB