

PRODUCT NUMBER
10034908-007LF







NOTE:
1. MATERIAL
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL 94 V-0 FLAME RETARDANT, BLACK.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING: CONTACT AREA: 30u" Au OVER 50u" Ni UNDER ALL
SOLDER TAIL: 100u" MATTE PURE TIN OVER 50u" Ni UNDER.

2. PRODUCT SPECIFICATION: GS-12-279.

3. PRODUCT PACKAGING SPEC: GS-14-937.

4. THIS CONNECTOR MEETS EUROPEAN UNION
DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED
IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDER APPLICATION
WITH A CIRCUIT BOARD.


5. MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.





rev	ecn no	dr	date
A	DG08-0073	JW	10/29/07
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 		tolerance std		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	JULIA WANG	10/29/07	ANGULAR		LINEAR	0.X	±0.5	size A4	Scale 1:1		
Eng	JULIA WANG	10/29/07				0.XX	±0.25				
Chr	GARY HSIEH	10/29/07	0°	±2°		0.XXX	±0.10				ECN
Appr	JOSEPH HSIA	10/29/07	Product family					Spec ref *			
		title	STRADDLE MOUNT TYPE				dwg no		10034908-007		Rev A
			catalog no				*	CUSTOMER COPY	sheet 1 of 2		


PRODUCT NUMBER
10034908-007LF




RECOMMENDED PCB LAYOUT FOR CONNECTOR MOUNTING
TYPICAL BOTH SIDES




SECTION A-A



DETAIL B
SCALE 4:1



RECOMMENDED MATING BOARD EDGE CONFIGURATION



www.fciconnect.com			surface 		tolerance std		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JULIA WANG	10/29/07	ANGULAR	LINEAR	0.X	±0.5	size A4	Scale 1:1		
Eng	JULIA WANG	10/29/07			0.XX	±0.25				
Chr	GARY HSIEH	10/29/07			0.XXX	±0.10				
Appr	JOSEPH HSIA	10/29/07	Product family					ECN DG08-0073		
			Spec ref					*		
	title STRADDLE MOUNT TYPE POWER EDGE CARD				dwg no 10034908-007				Rev A	
	catalog no				*		CUSTOMER COPY		sheet 2 of 2	