Part Number : 1200710038
Product Description : M12 Signal, A-Coded, Field-Attachable, 4 Poles, Male, Straight, PG7 Gland, 3.30-6.60mm
Series Number : 120071
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 8A4006-31



Documents and Resources

Drawings

1200710038_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:e36c436f-3855-4f47-aa15-3e18bd57ff7a
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	120071
Description	M12 Signal, A-Coded, Field-Attachable, 4 Poles, Male, Straight, PG7 Gland, 3.30-6.60mm
Approvals	cCSAus certified
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Field Attachable Connector
UPC	78678875700

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC / 300V DC

Physical

Cable Diameter	3.30-6.60mm (.130-.260")
Coupling Type	External Thread
Diagnostics / LEDs	No

Downloaded from Arrow.com.

Diagnostics Port	No
Gender	Male
Keyway	A-Coded
Material - Connector Body	PA
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	24.660/g
Orientation	Straight
Poles	4
Temperature Range - Operating	-25° to +90°C
Wire Size (AWG)	18

Downloaded from Arrow.com.