

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY- TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECR-17-014411	03OCT2017	BDA	MD

SUGGESTED MATING TAB





1 MATL: 1/2 H BRASS OR NICKEL PL STEEL.


2 NO BURRS PERMISSIBLE AT HOLE.


3 MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.


4 TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F

5 HOLE MUST BE SYMMETRICAL ABOUT TAB ℄ WITHIN 0.076 [.003]


* TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.








SECTION B-B



VIEW A-A



SECTION C-C

1 DIMENSIONS IN BRACKETS ARE IN INCHES.

2 PRODUCT PROVIED IN STRIP FORM, BREAKS MAY BE PRESENT.

3 THE 1.40 / 1.27 [.055 / .050] DIMENSION MUST BE MAINTAINED BY THE APPLICATOR CUT-OFF TO ENSURE THE PROPER LOCKING FUNCTION OF THE RECEPTACLE.

FINISH	INSULATION RANGE	WIRE SIZE	PART NO.
UNPLATED	1.52-2.54[.060-.100] DIA	[#22-#18] AWG	2238156-2
TIN PLATED	1.52-2.54[.060-.100] DIA	[#22-#18] AWG	2238156-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL: BRASS

FINISH: SEE TABLE

DWN 07OCT2016 NAGALAKSHMI K
CHK 07OCT2016 SMITH, RODNEY
APVD 07OCT2016 SMITH, RODNEY
PRODUCT SPEC —
APPLICATION SPEC 114-2074
WEIGHT 0

TE Connectivity

NAME: RECEPTACLE, POSITIVE LOCK, .250 SERIES —

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2238156	—

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV A2

2238156

Downloaded from Arrow.com.