

**Part Number :** 1720650304
**Product Description :** Mega-Fit Slim Vertical Header without Crush Pegs, 5.70mm Pitch, Through Hole, Dual Row, 4 Circuits, 0.76µm Gold (Au) Plating, 2.93mm Tail Length, Glow-Wire Capable, Tray, Black
**Series Number :** 172065
**Status :** Active
**Product Category :** PCB Headers and Receptacles

## Documents and Resources

### Drawings

1720650304_sd.pdf

768291100-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

768232000-AS-000.pdf

AS-76823-100-001.pdf

1720631000-PS-000.pdf

PS-76823-100-001.pdf

1720631000-TS-000.pdf

TS-76823-100-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |

Downloaded from Arrow.com.

| | |
|---|---|
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 172065 |
| Description | Mega-Fit Slim Vertical Header without Crush Pegs, 5.70mm Pitch, Through Hole, Dual Row, 4 Circuits, 0.76µm Gold (Au) Plating, 2.93mm Tail Length, Glow-Wire Capable, Tray, Black |
| Application | Wire-to-Board |
| Component Type | PCB Header |
| Product Name | Mega-Fit |
| UPC | 889056897280 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

Downloaded from Arrow.com.

| | |
|---|---|
| Current - Maximum per Contact | 27.0A |
| Voltage - Maximum | 600V AC (RMS)/DC |

**Physical**

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Black |
| Durability (mating cycles max) | 200 |
| First Mate / Last Break | No |
| Gender | Male |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Mated Height | 16.78mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Mounting Style | Through Hole |
| Net Weight | 2.398/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| Packaging Type | Tray |
| PCB Locator | Yes |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.58mm |
| PC Tail Length | 2.93mm |
| Pitch - Mating Interface | 5.70mm |
| Pitch - Termination Interface | 5.70mm |
| Plating min - Mating | 0.762µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Shrouded |

Downloaded from Arrow.com.

| | |
|---|---|
| Temperature Range - Operating | -40° to +120°C |
| Termination Interface Style | Through Hole |
| Unmated Height | 14.80mm |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Mega-Fit Dual Row Receptacle Housings | 170001 |
| Mega-Fit Dual Row Receptacle Housings | 171692 |
| Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assemblies | 245136 |



Downloaded from Arrow.com.