

Description

The DIODES™ AP43771 is a highly integrated USB Type-C® power delivery controller and targeted for USB Type-C adapter and charger application. It is compatible with Qualcomm® QC4/QC4+ protocol, which supports USB power delivery specification Rev3.0 V1.2 (including optional PPS support).

The AP43771 can support PPS APDO (Augmented Power Data Object) with 20mV/step voltage resolution and 50mA/step current resolution for power management. What's more, cable-loss compensation and SOP command for e-Marker detection are embedded too.

The AP43771 can provide robust protection scheme with built-in OVP/SCP/OTP features.

There are rich power functions embedded on the chip so as to reduce total BOM. A one-time-programmable ROM is provided for main firmware, and multi-time-programmable ROM is provided for user configuration data.


Features

- Compatible with USB PD Rev3.0 V1.2
- USB-IF PD3.0/PPS Certified TID = 1090028
- Qualcomm QC4/4+ Protocol Certificated
- OTP (One-Time-Programmable) for Main Firmware
- MTP (Multi-Time-Programmable) for System Configuration
- Built-in Regulator for CV and CC Control
- Support SCP/OTP/OVP/UVP with Auto Restart
- Support Power Saving Mode
- External N-MOSFET Control for VBUS Power Delivery
- Support e-Marker Cable Detection
- Operating Voltage Range: 3.3V to 16V
- Fewest External Component Count
- TID (1090028) for USB PD 3.0 PPS Compliance Test
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.**
<https://www.diodes.com/quality/product-definitions/>

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Pin Assignments

W-DFN3030-14 (Type A1)



Top View


Applications

- Type-C USB adapters/chargers
- USB PD converters

[illegible]

Pin Number	Pin Name	Function
1	VBUS	Output Terminal for Discharge Path.
2	PWR_EN	External NMOS Gate Driver. To control External MOS switch, 1: To enable VBUS voltage 0: Disconnect VBUS.
3	VCC	The Power Supply of the IC, connected to a ceramic capacitor.
4	ISENP	Input Current Sense Positive Node.
5	OCDRV	CC/CV Output. Open Drain Output for Opto-Coupler.
6	GND	Ground
7	OTP	Source Current to External NTC Sensor for OTP (Over Temperature Protection). Current amplitude is programmable.
8	VFB	CV Input. Negative Node of CV OPAMP for Opto-Coupler.
9	IFB	CC Input. Negative Node of CC OPAMP for Opto-Coupler.
10	CC2	Type-C_CC2
11	CC1	Type-C_CC1
12	DN	Type-C_DN
13	DP	Type-C_DP
14	V5V	LDO-5V Output

Functional Block Diagram



Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
V _{CC}	Input Voltage at VCC Pin	-0.3 to 24	V
V _{FBI} , V _{IFB} , V _{OTP}	Input Voltage at VFB, IFB, OTP Pins	-0.3 to 7	V
V _{BUS} , V _{PWR_EN} , V _{ISENP} , V _{OCDRV}	Input Voltage at VBUS, PWR_EN, ISENP, OCDRV Pins	-0.3 to 24	V
—	Voltage from PWR_EN to VCC Pin	-16 to 7	V
V _{V5V}	Input Voltage at V5V Pin	-0.3 to 7	V
V _{CC1} , V _{CC2}	Input Voltage at CC1, CC2 Pins	-0.3 to 7	V
V _{DP} , V _{DN}	Input Voltage at DP, DN Pins	-0.3 to 7	V
T _J	Operating Junction Temperature	-40 to +150	°C
T _{STG}	Storage Temperature	-65 to +150	°C
T _{LEAD}	Lead Temperature (Soldering, 10s)	+300	°C
θ _{JA}	Thermal Resistance (Junction to Ambient) (Note 5)	122	°C/W
θ _{JC}	Thermal Resistance (Junction to Case) (Note 5)	27	°C/W
—	ESD (Human Body Model) Voltage on DP, DN Pins	8	kV
—	ESD (Human Body Model) Voltage on VBUS, ISENP, PWR_EN, VCC, OCDRV, OTP, V5V, IFB, VFB, CC1, CC2 Pins	2	kV
—	ESD (Charged Device Model)	750	V

Notes: 4. Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.
5. Test condition: Device mounted on FR-4 substrate PC board, 2oz copper, with the minimum footprint.

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V _{CC}	Power Supply Voltage	3.3	16	V
T _{OP}	Operating Temperature Range	-40	+85	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
VCC PIN SECTION						
V _{ST}	Startup Voltage	—	2.7	2.8	3.2	V
V _{UVLO}	Minimum Operating Voltage	—	2.6	2.7	3	V
V _{CC_HYS}	V _{CC} Hysteresis (V _{ST} -V _{UVLO})	—	0.1	—	—	V
I _{CC_DEEP SLEEP}	V _{IN} Current in Deep Sleep Mode	CC1/2 Detach after 3s	—	550	700	μA
I _{CC_OPR}	Operating Supply Current	—	—	3.3	6	mA
VOLTAGE CONTROL LOOP SECTION						
V _{REF_CV5}	Reference Voltage for 5V CV Control	—	0.49	0.5	0.51	V
V _{REF_CV9}	Reference Voltage for 9V CV Control	—	0.88	0.90	0.92	V
V _{REF_CV12}	Reference Voltage for 12V CV Control	—	1.17	1.20	1.23	V
V _{CABLE}	Cable Compensation (Note 6)	—	24	30	36	mV/A
I _{OS}	Maximum OCDRV Pin Sink Current	V _{OUT} = 4V	10	16	30	mA
PROTECTION FUNCTION SECTION						
V _{OVP5V}	OVP_5V Enable Voltage (Note 7)	—	5.5	6	6.5	V
V _{OVP9V}	OVP_9V Enable Voltage (Note 7)	—	9.9	10.8	12.1	V
V _{OVP12V}	OVP_12V Enable Voltage (Note 7)	—	13.2	14.4	16.2	V
t _{DEBOUNCE_OVP}	OVP Debounce Time (Note 9)	—	—	90	—	ms
V _{UVP5V}	UVP_5V Enable Voltage	—	3.4	3.8	4.2	V
V _{UVP9V}	UVP_9V Enable Voltage	—	6.1	6.8	7.5	V
V _{UVP12V}	UVP_12V Enable Voltage	—	8.2	9.1	10	V
I _{OVD}	Over Voltage Discharge Current	—	—	240	—	mA
t _{OCP}	OCP Deglitch Time (Note 8)	—	—	30	—	ms
t _{RESTART_INTERVAL_SCP}	Restart Interval Time under SCP (Note 8)	—	—	0.8	—	s
T _{OTP}	Internal OTP Temperature	—	—	+140	—	°C
I _{OTP_EXTERNAL}	External OTP Current	—	—	100	—	μA

Notes:

6. Cable compensation voltage can be adjusted by setting from 0 to V_{CABLE}*N, (N: 0 to 7).
7. 120% OVP setting.
8. Guaranteed by design.
9. OVP blanking time during V_O transition from high output voltage to low output voltage, such as 9V to 5V, or 12V to 5V.

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.) (continued)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
PROTECTION FUNCTION SECTION						
T _{HYS}	OTP Recovery Hysteresis Temperature	—	—	+25	—	°C
t _{SLEEP}	Enter Sleep Mode Time after Cable Detached (Note 8)	—	—	3	—	s
t _{OV_DELAY}	Delay from OVP Threshold Trip to NMOS Gate Turn-Off (Note 8)	—	—	—	50	μs
t _{UV_DELAY}	Delay from UVP Threshold Trip to NMOS Gate Turn-Off (Note 8)	—	—	30	—	ms
CC1/CC2, DP/DN PIN SECTION						
V _{L_RD3A}	Low Voltage Threshold Used to Distinguish R _D Attached or Detached for 3A Delivery	—	—	1.35	—	V
V _{H_RD3A}	High Voltage Threshold Used to Distinguish R _D Attached or Detached for 3A Delivery	—	—	2.0	—	V
I _{RD3A}	CC1/CC2 Current Source for 3A Advertisement	—	304	330	356	μA
V _{OVP_DN}	DN Line Over Voltage Protection Threshold	—	4.2	4.5	4.8	V
V _{OVP_DP}	DP Line Over Voltage Protection Threshold	—	4.2	4.5	4.8	V

Note: 8. Guaranteed by design.

Performance Characteristics

System Power-On Sequence:

When the external power source is provided, the AP43771 will wake up, and the USB PD controller and MCU will be initialized. All analog control blocks are ready and waiting for PD negotiation process. Meanwhile, the AP43771 monitors the voltage and current conditions to prevent abnormal conditions from happening. Once any unacceptable condition happens, the AP43771 will go into protection procedure according to the types of abnormal conditions.

Voltage Transition

According to USB PD's protocol, the PD device requests different power profile and the AP43771's power control blocks will change voltage and current values. The AP43771 provides corresponding Over Voltage Protection (OVP), Over Current Protection (OCP) scheme, and feedback system stability to guarantee monotonic voltage transition and avoid violating USB PD electrical specification.

The AP43771 provides zero-mismatch voltage methodology that is more flexible for customer system design requirement. When UFP/DFP makes an acceptable power request deal, the AP43771 will change the VFB pin voltage according to the USB PD command. The voltage regulator control loop regulates the required V_{BUS} voltage according to V_{FB} . In addition, the shunt regulator is built in to minimize the total external components and cost.

Protection

The AP43771 provides OVP/UVP/OCP/SCP/OTP functions and also support Constant Current (CC) function. All of the protection thresholds depend on the requested power profile, and provide the most reliable protection scheme.


The AP43771 provides OVP feature by turning off the power switch when V_{BUS} is higher than OVP enable voltage. Meanwhile, it provides internal discharge path to reduce the overvoltage duration, and terminates discharge current as soon as V_{BUS} reaches the target voltage. To prevent the V_{BUS} pin from working abnormally, the AP43771 provides UVP function whenever V_{BUS} drops to UVP enable voltage.

To ensure the safe operation of USB PD, the AP43771 provides programmable OCP function to make sure output current will not be higher than the allowed maximum current. Once OCP conditions happen, the AP43771 will shut down the USB PD system and send "Hard Reset" to the Upstream-Facing Port (UFP) device.

CV/CC

The AP43771 supports Constant Voltage (CV) and Constant Current (CC) functions to control the output voltage and the output current by the control pin OCDRV. During the CV mode, the AP43771 operates in fixed PDO, and the output voltage will be regulated to the requested voltage if the output current is below the allowed maximum current. Once the sink device draws more than I_{OCP} , the over current protection will be triggered. When the CC mode function is enabled, the output voltage drops, and the source current is limited within 150mA whenever output current exceeds the allowed maximum current. When the output voltage drops below UVP, constant current limit turns off V_{BUS} and starts error recovery procedure. The AP43771 will reset if the voltage continues dropping to UVLO threshold.


Ordering Information



Part Number	Part Number Suffix	Package	Identification Code	Packing	
				Qty.	Carrier
AP43771FBZ-13-FXX	-13	W-DFN3030-14 (Type A1)	3V	3000	Tape and Reel

Marking Information

(Top View)




3V : Identification Code
Y : Year : 0 to 9
W : Week : A to Z : week 1 to 26;
 a to z : week 27 to 52; z represents
 week 52 and 53
X : Internal Code

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


W-DFN3030-14 (Type A1)



Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

W-DFN3030-14 (Type A1)



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

DIODES is a trademark of Diodes Incorporated in the United States and other countries.
The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
© 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com