









APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/13/17	
A		UPDATE DRAWING	7/15/19	AY/NL



SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: White

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 125 V AC/DC.

Current rating: 2A AC/DC.

Contact resistance: 20 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 15

A = .079 [2.00] x No. of Spaces

B = .079 [2.00] x No. of Spaces + .157 [4.00]

C = .079 [2.00] x No. of Spaces + .122 [3.10]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 Ø.X ± .10
 .XX ± .020 Ø.XX ± .015
 .XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	11/13/17
CHECKED	RC1	11/13/17
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE .079 [2.00] WAFER, PCB TYPE, RIGHT ANGLE
 TIN PLATED, INSULATOR COLOR WHITE

SIZE	PART NO.	REV.
X	2SH-F-XX-TR-WT	A
REF:	S00186T	SCALE: NTS
SHEET 1 OF 1		