

Industrial Axial Cemented Leaded Wirewound Resistors



The Z300 series, is the perfect choice for high power, high current applications. This product series is tested to meet challenging operating and ambient conditions. Typical applications include but are not limited to home appliances, lighting ballast, etc.

FEATURES

- All welded construction
- Non flammable cement coating
- Ceramic core
- Various kinds of lead forming available
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- Appliances (washing machine, ovens)
- Ballast
- TV
- Power supply

STANDARD ELECTRICAL SPECIFICATIONS				
TYPE	POWER RATING P_{40}	RESISTANCE RANGE	TEMPERATURE COEFFICIENT	RESISTANCE TOLERANCE
Z301	1 W	0.30 Ω to 270 Ω	-10 ppm/K to -80 ppm/K	$\pm 10\%$, $\pm 5\%$
		0.68 Ω to 2 k Ω	100 ppm/K to 180 ppm/K	
ZDA0411	2 W	0.47 Ω to 560 Ω	-10 ppm/K to -80 ppm/K	$\pm 10\%$, $\pm 5\%$
		1.50 Ω to 4.30 k Ω	100 ppm/K to 180 ppm/K	
ZDV0411	2 W	0.47 Ω to 560 Ω	-10 ppm/K to -80 ppm/K	$\pm 10\%$, $\pm 5\%$
		1.50 Ω to 4.30 k Ω	100 ppm/K to 180 ppm/K	
Z302	3 W	0.10 Ω to 510 Ω	-10 ppm/K to -80 ppm/K	$\pm 10\%$
		1.80 Ω to 3.30 k Ω	100 ppm/K to 180 ppm/K	
		0.10 Ω to 510 Ω	-10 ppm/K to -80 ppm/K	$\pm 5\%$
		24 Ω to 3.30 k Ω	100 ppm/K to 180 ppm/K	
		0.22 Ω to 510 Ω	-10 ppm/K to -80 ppm/K	
1 Ω to 510 Ω	-10 ppm/K to -80 ppm/K	$\pm 1\%$		
Z303	4 W	0.10 Ω to 1 k Ω	-10 ppm/K to -80 ppm/K	$\pm 10\%$
		1.80 Ω to 3.90 k Ω	100 ppm/K to 180 ppm/K	
		0.10 Ω to 1 k Ω	-10 ppm/K to -80 ppm/K - 10 ppm/K to - 80 ppm/K	$\pm 5\%$
		12 Ω to 3.90 k Ω	100 ppm/K to 180 ppm/K	
		0.10 Ω to 1 k Ω	-10 ppm/K to -80 ppm/K	
		1 Ω to 1 k Ω	-10 ppm/K to -80 ppm/K	$\pm 1\%$
Z307	10 W	0.20 Ω to 8.2 k Ω	-10 ppm/K to -80 ppm/K	$\pm 10\%$, $\pm 5\%$
		12 Ω to 30 k Ω	100 ppm/K to 180 ppm/K	
		1.80 Ω to 8.2 k Ω	-10 ppm/K to -80 ppm/K	$\pm 2\%$
		3.30 Ω to 8.2 k Ω	-10 ppm/K to -80 ppm/K	$\pm 1\%$



PACKAGING							
TYPE	CODE	DESCRIPTION	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	DIMENSIONS
Z301	21	A1 G53	1000	Taped acc. to IEC 60286-1 fan-folded in a box	53 mm	5 mm	324 mm x 79 mm x 75 mm
	D2	R2 R53	2000	Taped acc. to IEC 60286-1 in a reel	53 mm	5 mm	260 mm x 260 mm x 95 mm
ZDA0411	41	A1 G73	1000	Taped acc. to IEC 60286-1 fan-folded in a box	73 mm	5 mm	324 mm x 101 mm x 64 mm
ZDV0411	40	A2 G73	2000	Taped acc. to IEC 60286-1 fan-folded in a box	-	12.7 mm	334 mm x 157 mm x 53 mm
Z302	2C	AC G53	500	Taped acc. to IEC 60286-1 fan-folded in a box	53 mm	5 mm	324 mm x 82 mm x 49 mm
	24	A4 G53	4000	Taped acc. to IEC 60286-1 fan-folded in a box	53 mm	5 mm	380 mm x 75 mm x 170 mm
	25	A4 G63	4000	Taped acc. to IEC 60286-1 fan-folded in a box	63 mm	5 mm	380 mm x 85 mm x 200 mm
	4C	AC G73	500	Taped acc. to IEC 60286-1 fan-folded in a box	73 mm	5 mm	324 mm x 101 mm x 49 mm
	6C	AC G83	500	Taped acc. to IEC 60286-1 fan-folded in a box	83 mm	10 mm	324 mm x 111 mm x 75 mm
	D2	R2 R53	2000	Taped acc. to IEC 60286-1 in a reel	53 mm	5 mm	260 mm x 260 mm x 95 mm
	H1	R1 R83	1000	Taped acc. to IEC 60286-1 in a reel	83 mm	10 mm	260 mm x 260 mm x 125 mm
	LC	LC	500	Bulk Packing	94 mm ⁽¹⁾	-	225 mm x 140 mm x 140 mm
Z303	2C	AC G53	500	Taped acc. to IEC 60286-1 fan-folded in a box	53 mm	5 mm	324 mm x 79 mm x 75 mm
	6C	AC G83	500	Taped acc. to IEC 60286-1 fan-folded in a box	83 mm	10 mm	324 mm x 111 mm x 90 mm
	LC	LC	500	Bulk Packing	94 mm ⁽¹⁾	-	225 mm x 140 mm x 140 mm
	D1	R1 R53	1000	Taped acc. to IEC 60286-1 in a reel	53 mm	10 mm	260 mm x 260 mm x 125 mm
	H1	R1 R83	1000	Taped acc. to IEC 60286-1 in a reel	83 mm	10 mm	260 mm x 260 mm x 95 mm
Z307	LJ	LJ	200	Bulk Packing	120 mm ⁽¹⁾	-	225 mm x 140 mm x 140 mm

Note

⁽¹⁾ For bulk packing, defined width is end-to-end length and not inner tape width



PART NUMBER AND PRODUCT DESCRIPTION																	
Part Number: Z32041411509K2C000																	
Z	3	2	0	4	1	4	1	1	5	0	9	K	2	C	0	0	0
TYPE	TCR / MATERIAL	VALUE	TOLERANCE CODE	PACKAGING CODE	SPECIAL												
Z310309 = Z301 ZDA0411 = ZDA0411 ZDV0411 = ZDV0411 Z320414 = Z302 Z330617 = Z303 Z370947 = Z307	1 = -10 ... -80 ppm/K WM 50 Class 1 3 = 100 ... 180 ppm/K WM 110 Class 3 4 = SWI (special winding)	3 digit value 1 digit multiplier MULTIPLIER 7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ²	F = ± 1.0 % G = ± 2.0 % J = ± 5.0 % K = ± 10.0 %	(see Packaging table)	The 5 digit BV number will be encoded using a 36 character code. This code contains numbers 0...9 and letters A...Z (36 characters total) and allows to encode at least 46 655 five digit BV numbers. 000 = standard												
Product Description: Z302 1 15R 10 % AC G53																	
Z302	1	15R	10 %	AC G53													
TYPE	TCR / MATERIAL	VALUE	TOLERANCE CODE	PACKAGING DESCRIPTION													
Z301 ZDA0411 ZDV0411 Z302 Z303 Z307		2K0 4K3	1 % 2 % 5 % 10 %	A1 G53 AC G73 R2 R53 LJ A1 G73 AC G83 A2 G73 R1 R83 AC G53 LC A4 G53 AC G83 A4 G63 R1 R53													



DESCRIPTION

Wirewound resistors are best suited for use in high power, high current applications. The silicon cement lacquer coating enables Z300 to withstand challenging operating and environmental conditions.

The coating is resistant to cleaning solvents specified in IEC 60115-1 ⁽¹⁾. Production is strictly controlled and follows an extensive set of instructions established for reproducibility. The winding is done with a specific material on a specially developed fine ceramic body (Al₂O₃). The ceramic meets the highest requirements against mechanical resistance, thermal shocks, dielectric strength, and insulation resistance at high temperatures. With different diameters and turn spacing's, a large ohmic value range can be covered. The resistors are marked with resistance and tolerance.

Product quality is verified by testing procedures, performed on all individual resistors. Resistance is measured on the lead wires at a distance of 6 mm from the resistor body. If a greater length of lead wire is used in the application, the user may need to consider the additional wire resistance, particularly with low resistance products.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽²⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽³⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁴⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree. Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

Notes

- ⁽¹⁾ Other cleaning solvents with aggressive chemicals should be evaluated in actual cleaning process for their suitability
- ⁽²⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- ⁽³⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
- ⁽⁴⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>

ASSEMBLY

The resistors are axial leaded for soldering. The terminals of the resistors are completely lead (Pb)-free, the special tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes.

Special lead forms may be available on request, please inquire at ww1resistors@vishay.com.

These components are high dissipation power resistors, customers are advised to use a high melting point solder.

APPLICATION INFORMATION

The power dissipation of the resistor generates a temperature rise with respect to the ambient. The permissible dissipation is derated for temperatures above 40 °C, as shown in the derating diagram, in order to avoid overheating of the resistor. The heat dissipated from the resistor may affect adjacent components, hence proper clearance will be required in order to avoid overheating. The resistive wire is hermetically encapsulated.

All materials used are non-flammable and inorganic.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.





RELATED PRODUCTS

In similar applications and high dissipation conditions, see the datasheets:


- AC Series - Cemented Wirewound Resistors
www.vishay.com/doc?28730
- Z300-Cxx - High Surge Axial Cemented Wirewound Resistors
www.vishay.com/doc?21027

For precision applications, there is the cement coated PAC series, see the datasheet:

- PAC Series - Cemented Wirewound Precision Resistors
www.vishay.com/doc?28731

FUNCTIONAL PERFORMANCE

Derating

Temperature Rise

Temperature Rise

Temperature Rise
TEST PROCEDURES AND REQUIREMENTS


IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ($\Delta R_{MAX.}$)
4.13	-	Short time overload	Room temperature; 10 x rated power P_{40} ; 5 s	$\pm (1 \% R + 0.1 \Omega)$
4.16	21 (Ua ₁) 21 (Ub) 21 (Uc)	Robustness of terminations	Tensile, bending and torsion	No damage $\pm (0.5 \% R + 0.05 \Omega)$
4.18	20 (Tb)	Resistance to soldering heat	Unmounted components (260 \pm 5) °C; (10 \pm 1) s	$\pm (0.5 \% R + 0.05 \Omega)$
4.24	78 (Cab)	Damp heat, (steady state)	56 days; (40 \pm 2) °C; (93 \pm 3) % RH	$\pm (3 \% R + 0.1 \Omega)$
4.25.2	-	Endurance (at room temperature)	1000 h; loaded with 116 % of P_{70} ; 1.5 h ON and 0.5 h OFF	$\pm (3 \% R + 0.1 \Omega)$
4.25.3	-	Endurance (at 200 °C)	1000 h; without load	$\pm (3 \% R + 0.1 \Omega)$

DIMENSIONS


TYPE	DIMENSIONS in millimeters [inches]				
	L _{MAX.}	D _{MAX.}	d	B	MASS (g)
Z301	8.5 [0.355]	3 [0.118]	0.7 [0.027]	53 ± 1 [2.087 ± 0.039]	0.5
ZDA0411	11 [0.433]	4 [0.157]	0.7 [0.027]	53 ± 1 [2.087 ± 0.039]	0.8
Z302	13 [0.512]	4.8 [0.189]	0.8 [0.031]	53 ± 1 [2.087 ± 0.039]	1.1
Z303	15.8 [0.622]	5.5 [0.217]	0.8 [0.031]	53 ± 1 [2.087 ± 0.039]	1.4
Z307	49.8 [1.961]	9 [0.354]	0.8 [0.031]	120 ⁽¹⁾ ± 2 [4.724 ± 0.079]	7

Note

⁽¹⁾ For Z307, dimension "B" is resistor end-to-end length and not inner tape width

DIMENSIONS ZDV0411


DIMENSIONS in millimeters			TOL.
Lead Ø	d	0.6	-
Pitch of components	P	12.7	± 1.0
Pitch of sprocket holes ⁽¹⁾	P ₀	12.7	± 0.3
Distance between hole center and resistor center	P ₁	3.85	± 0.7
Distance between hole center and lead center	P ₂	6.35	± 0.7
Lead spacing	F	5	+0.6, -0.1
Angle of Insertion	Δh ₁	2 max.	-
Width of carrier tape	W	18.0	+1, -0.5
Width of adhesive tape	W ₀	12.0	± 0.5
Position of holes	W ₁	9	+0.75, -0.5
Position of adhesive tape	W ₂	0.5	+0, -0.5
Body to hole center	H	16.0	± 0.5
Lead crimp to hole center ⁽²⁾	H ₀	19.5	± 1.0
Hole Ø	D ₀	4.0	± 0.2
Thickness of tape ⁽³⁾	t	0.9 max.	-
Height of cutting	L	11 max.	-
Height of insertion	H ₁	32.3 max.	-

Notes

- ⁽¹⁾ Test over 10 holes - 9 intervals P₀ 12 x 9 = 114.3 ± 0.5
- ⁽²⁾ Parallelism, < 0.5 mm
- ⁽³⁾ Thickness of carrier tape: 0.55 mm ± 0.1



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.