



Part Number : [2047110101](#)
Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Vertical, Surface Mount, 0.76µm Gold (Au) Plating, 2.50mm Solder Tab
Series Number : 204711
Status : Active
Product Category : I/O Connectors



Documents & Resources

Drawings
[2047110101_sd.pdf](#)

3D Models and Design Files
[2047110101_stp.zip](#)

Specifications
[PS-105448-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	204711
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Vertical, Surface Mount, 0.76µm Gold (Au) Plating, 2.50mm Solder Tab
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 3.1
Type	C
UPC	193264115617

Electrical

Current - Maximum per Contact	0.25A,1.25A,5.0A, See Product Specification
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC/DC

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	None

Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Vertical
Net Weight	0.687/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	No
Ports	1
Temperature Range - Operating	-30° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
USB Shielded I/O Type C Plugs	<u>105444</u>

This document was generated on Dec 06, 2024